

ANT-LTE-HDP-2000-SMA ✓ ACTIVE

TE Internal #: L9000174-01

Module Antenna, Wide Band, LTE / Cellular, Remote Mount, Adhesive, SMA, Omnidirectional, Single Port, Gain > 6 dBi

[View on TE.com >](#)



Antennas



Wireless Application: **Cat-M/NB-IoT, Cellular, LTE**

Mounting Location: **Remote**

Mounting Type: **Adhesive**

Antenna Termination: **SMA**

Antenna Type: **Module**

Features

Product Type Features

Antenna Product Type	Antenna
Antenna Termination	SMA

Configuration Features

Antenna Style	Whip
Mounting Location	Remote
Antenna Type	Module
Band Type	Wide Band
Port Configuration	Single Port

Electrical Characteristics

VSWR (Max)	<1.8:1
Impedance	50 Ω

Signal Characteristics

Gain (Max)	3.5 dB
Frequency Band	698 – 960 MHz
Nominal Frequency Range	617 – 6000
Peak Gain	> 6 dBi

Body Features

Product Weight	42 g[1.48148 oz]
----------------	------------------



Mechanical Attachment

Polarization	Linear
Mounting Type	Adhesive

Dimensions

Cable Length	2 m[6.56 ft]
Product Width	17 mm[.67 in]
Product Length	104 mm[4.09 in]
Product Height	4.2 mm[.17 in]

Operation/Application

Directionality	Omnidirectional
----------------	-----------------

Industry Standards

IP Rating	IP67
Wireless Application	Cat-M/NB-IoT, Cellular, LTE
Primary Application	Cellular, LTE

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the

product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # CONSMA001
SMA Jack 50 Ohm PCB Through Hole



TE Part # CONSMA002-L-G
SMA Jack 50 Ohm PCB Through Hole



TE Part # CONSMA002-SMD-G
SMA Jack 50 Ohm PCB Surface Mount



TE Part # CONSMA008-G
SMA Jack 50 Ohm Through Hole PCB



TE Part # L000795-15
Antenna LTE VDP Adh Bk 1.5M
FAKRA-C Plug


Customers Also Bought



TE Part # T4130512041-000
M12, REAR MOUNT, MALE, D, 4P,
SOLDER WIRE



TE Part # T4112502041-000
M12, FEMALE, RA, D CODE, 4P, PG9,
GOLD



TE Part # 1-215307-2
2X12P HV100 REC CON. TE, 7.0MM



TE Part # TAD14841311-001
M12D4-MS-MR-PVC TYPE B RED-0.5M




TE Part # 4-1618413-9
EV600HSANM = CONTACTOR, SPST-
NO 24V COIL



TE Part # L9000176-01
Antenna Vert 1/2 Wave Dipole LTE 2M
SMA



TE Part # ANT-LTE-WS-SMA
Antenna Blade NBIOT LTE-M Swivel
SMA



TE Part # 5-2176422-9
TLRP 2512 3.0W R022 1% 50PPM 4K RL



Documents

Product Drawings

[Antenna Horiz 1/2 Wave Dipole LTE 2M SMA](#)

English

Datasheets & Catalog Pages

[Sub-6 Cellular LTE-5G NR Frequency Band Guide](#)

English

[Remote Adhesive-Mount Cellular Antenna](#)

English

[Virtual Antenna](#)

English

[Microslatch Ground Plane Optimization](#)

English