



Specific SP6T Ramses SMA 18GHz Latching 28Vdc D-SUB Male Connector Bipolar Actuator Command for cryogenic application

PAGE 1/2 ISSUE 23-02-21 SERIE : SPnT PART NUMBER : R583423141

#### RF CHARACTERISTICS\*

Number of ways : 6

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18
VSWR max	1.20	1.30	1.40	1.50
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB
Isolation min	80 dB	70 dB	60 dB	60 dB

	Average power (**)	240 W	150 W	120 W	100 W
--	--------------------	-------	-------	-------	-------

Cryogenic characteristics are not measured during product acceptance test. RF performances are based on customers test reports.

#### **ELECTRICAL CHARACTERISTICS**

Actuator\*\*\* : LATCHING
Nominal current at 25°C (±10%) : 62.5 mA

Actuator voltage (Vcc) : 28V (24 to 30V)

Terminals : 15 pins D-SUB male connector

# MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012 Life : 5.000.000 cycles per position

Switching Time (nominal voltage at 25°C) : <15 ms

Construction : Splashproof

Weight : <180 g

### **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range : -273°C to +85°C
Storage temperature range : -273°C to +85°C

(\* Specified with only one way switched) (\*\* Average power at 25°C per RF Path)

(\*\*\* More than one position can be switched at the same time)




PEN20189059			
Name : VB	23-02-21	Update informations	FJ
Date: 23/02/2021	Issue	Revision	App.

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.






Specific SP6T Ramses SMA 18GHz Latching 28Vdc D-SUB Male Connector Bipolar Actuator Command for cryogenic application



## SCHEMATIC DIAGRAM

To reduce impact on system temperature, the same magnetic field can be applied with half current. Reset can be accomplished by reversing the direction of current in the circuit.



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.