


Technical Data Sheet

DPDT Ramses SMA 3GHz Failsafe 28Vdc Diodes D-sub connector with bracket

RF CHA	RACTERIS	STICS			
	requency ra	ange		∷ 0 - 3 GHz ∷ 50 Ohms	
V In Is	requency ((SWR max sertion loss olation min verage pow	s max	DC - 3 1.20 0.20 dB 80 dB 240 W		
ELECTR	RICAL CHA	RACTERIS	<u>FICS</u>		
N A	ctuator ominal curr ctuator volt erminals			∷ FAILSAFE ∷ 140 mA ∷ 28V (24 to 3 ∷ 9 pins D-SU	30V) JB male connector
MECHA	NICAL CH/	ARACTERIS	TICS		
Li S C	onnectors fe witching Tir onstruction /eight			: SMA female : 2.5 million o : < 15 ms : Splashproo : < 100 g	
ENVIRC	NMENTAL	CHARACT	ERISTICS		
		mperature ra		∵ -40°C to +8 ∶ -55°C to +8	
(** A	t 25° C ±10		er RF Path)		· COMPLIAN

Technical Data Sheet

DPDT Ramses SMA 3GHz Failsafe 28Vdc Diodes D-sub connector with bracket



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.