

# **Multilayer Ceramic Chip Capacitor**

Part Number: 1812JA250101JKTSYS

1812 250Vac (Y2), 305Vac (X1), 50/60Hz / **Description:** 1000Vdc 100pF ±5% C0G/NP0 (1B) to AEC-

Q200

Approval IEC/EN60384-14:2013+A1

Specifications: UL60384-14, CAN/CSA E60384-14:14


Certification: TÜV R60153663 / ID1111233478

UL/cUL E228790-20201127

Classification: IEC/EN 60384-14:2013+A1 Class Y2 / X1 for use

in equipment within the spec of IEC62368

UL/cUL FOWX2, FOWX8



Component Marking and Certification Bodies:



Material Group I : CTI >= 600

### **Mechanical Specification**

Size Code 1812

Length (L1) in mm (")  $4.8 \pm 0.35$  (0.189  $\pm 0.014$ ) Width (W) in mm (")  $3.2 \pm 0.30$  (0.126  $\pm 0.012$ )

Thickness (T) in mm (")

1.5 Max (0.06 Max)

Minimum Termination Band (L2,L3) in mm (") 0.35 (0.014)

Maximum Termination Band (L2,L3) in mm (") 0.80 (0.030)

Minimum Band Gap (L4) in mm (") 3.5 (0.138)

Termination Material Nickel Barrier, Sn Plated Solder (RoHS compliant)

Solderability IEC-60068-2-58

Packaging 7" Reel Horizontal Orientation, 500 per reel

## **General Electrical Specification**

Rated Voltage

Humidity Grade

Maximum DC Working Voltage Nominal Capacitance Value

Capacitance Tolerance

Tangent of Loss Angle (Tan  $\delta$ )

Capacitance and Tan δ Test Conditions

Voltage Proof

(50mA max charging current for DC tests)
Min Insulation Resistance (IR)
Dielectric Classification

Rated Temperature Range

Maximum Capacitance Change over Temperature Range

Climatic Category (IEC)
Ageing Characteristic

Class Y2\* (250Vac), Class X1\* (305Vac), 50/60Hz, 5kV impulse (\*Applicable to equipment within the scope of IEC 62368)

Grade III (IEC/EN60384-14:2013 Annex 1)

1000Vdc certified / (2500Vdc outside scope of any specification)

100pF ±5%

≤0.0015

1.0Vrms @ 1MHz

100% test: 3000Vdc 1s min / 5s max

AQL test: 3225Vdc / 2110Vac 60s min / 5kV 1.2x50µs impulse

100.00GOhm @ 100Vdc C0G/NP0 (1B) to AEC-Q200

-55°C / +125°C

No DC Voltage 0±30ppm/°C

Rated DC Voltage -

55/125/56 Zero

\_\_\_\_

Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com

Asia: KPD-Asia-sales@knowles.com

Asia. KPD-Asia-sales@kilowies.com

USA: KPD-NA-sales@knowles.com

www.knowlescapacitors.com

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at http://www.knowlescapacitors.com or by contacting us.

© The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consent of Knowles and any customer mentioned within this specification.

Data is correct to the best of our knowledge, errors and

omissions excepted.

Date: Thursday, September 02, 2021

20210902 192732137UTC



# **Multilayer Ceramic Chip Capacitor**

Part Number: 1812JA250101JKTSYS

**Description:** 

1812 250Vac (Y2), 305Vac (X1), 50/60Hz / 1000Vdc 100pF ±5% C0G/NP0 (1B) to AEC-

Q200

#### **Environmental**

RoHS Compliant to 2011/65/EC as amended by 2015/863/EU

Compliant

**REACH Compliant** 

211 compliant

California Proposition 65

No exposure risk


### **Board Layout**

Knowles' conventional 2-terminal chip capacitors can generally be mounted using pad designs in accordance with international specification IPC-7351, Generic Requirements for Surface Mount Design and Land Pattern Standards, but there are some other factors that have been shown to reduce mechanical stress, such as reducing the pad width to less than the chip width. In addition, the position of the chip on the board should be considered.

Some high voltage parts may require modifications to the board layout and/or the addition of a conformal coating to prevent flashover. Refer to application note AN0043 for further information.

#### IPC-7351 pad design


	1812	
С	4.00mm	0.157"
Υ	1.55mm	0.061"
Х	3.40mm	0.134"



## **Packaging**

Tape packaging information for tape-and-reel parts:

Tape and reel packing of surface mounting chip capacitors for automatic placement are in accordance with IEC60286-3.




## Soldering

Reflow solder in accordance with IPC-A-610. Recommended reflow profile as laid down in IPC/JEDEC J-STD-020.

Wave soldering is also possible, but care must be taken for case sizes 1210 and larger and component thickness >1.0mm. Trials are encouraged.

Hand soldering is not recommended and can lead to component damage through thermal shock.

DLI



Application notes with mounting and handling guidance are available on request.

Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com

Compex

Asia: KPD-Asia-sales@knowles.com

USA: KPD-NA-sales@knowles.com

www.knowlescapacitors.com

Johanson MFG

Novacap

Syfer

Voltronics

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at http://www.knowlescapacitors.com or by contacting us.

The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consent of Knowles and any customer mentioned within this specification. Data is correct to the best of our knowledge, errors and omissions excepted.

отполого охоортов.

Date: Thursday, September 02, 2021