# **Technical Data Sheet**



DPDT Ramses SMA2.9 40GHz Latching Indicators 28Vdc Pins Terminals with bracket

PAGE 1/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577843000

## **RF CHARACTERISTICS**

Frequency range : 0 - 40 GHz Impedance : 50 Ohms

| Frequency (GHz)    | DC - 6  | 6 - 12.4 | 12.4 - 18 | 18 - 26.5 | 26.5 - 40 |
|--------------------|---------|----------|-----------|-----------|-----------|
| VSWR max           | 1.30    | 1.40     | 1.50      | 1.70      | 1.90      |
| Insertion loss max | 0.30 dB | 0.40 dB  | 0.50 dB   | 0.70 dB   | 0.80 dB   |
| Isolation min      | 70 dB   | 60 dB    | 60 dB     | 55 dB     | 50 dB     |
| Average power (*)  | 80 W    | 60 W     | 50 W      | 20 W      | 10 W      |

## **ELECTRICAL CHARACTERISTICS**

Actuator : LATCHING
Nominal current \*\* : 125 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / NEGATIVE COMMON Terminals : solder pins (250°C max. / 30 sec.)

Indicator rating : 1 W / 30 V / 100 mA

# MECHANICAL CHARACTERISTICS

Connectors : SMA 2.9 female per MIL-C 39012

Life : 2.5 million cycles

Switching Time\*\*\* : < 15 ms

Construction : Splashproof

Weight : < 100 g

# **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(\* Average power at 25°C per RF Path)

(\*\* At 25° C ±10%)

(\*\*\* Nominal voltage; 25° C)




# **Technical Data Sheet**





DPDT Ramses SMA2.9 40GHz Latching Indicators 28Vdc Pins Terminals with bracket

PAGE 2/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577843000

## **DRAWING**








General tolerances: ±0,5 mm [0,02 in]

## SCHEMATIC DIAGRAM



# LABEL 1 2 5 RADIALL® R577843000 0 - 40 GHz Un : 28V Lot : \_\_\_\_

| Voltage | RF Continuity                                   | Ind. |
|---------|---|------|
| -C +1   | $1 \leftrightarrow 3 \ / \ 2 \leftrightarrow 4$ | C.1  |
| -C +2   | $1 \leftrightarrow 2 / 3 \leftrightarrow 4$     | C.2  |