# **Technical Data Sheet**



SP4T Ramses SMA2.9 40GHz Latching Self-cut-off Auto-reset 12Vdc
TTL Diodes Pins Terminals

SERIE : SPnT PART NUMBER : R573882420

#### RF CHARACTERISTICS

PAGE 1/2

Number of ways : 4

ISSUE **22-03-22** 

Frequency range : 0 - 40 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 6	6 - 12.4	12.4 - 18	18 - 26.5	26.5 - 40
VSWR max	1.30	1.40	1.50	1.70	2.20
Insertion loss max	0.20 dB	0.40 dB	0.50 dB	0.70 dB	1.10 dB
Isolation min	70 dB	60 dB	60 dB	55 dB	50 dB
Average power (*)	40 W	30 W	25 W	15 W	5 W

#### **ELECTRICAL CHARACTERISTICS**

Actuator : LATCHING
Nominal current \*\* : 640 mA

Actuator voltage (Vcc) : 12V (10.2 to 13V)

Terminals : solder pins (250°C max. / 30 sec.)

Self cut-off time : 40 ms < CT < 120 ms

TTL inputs (E) - High level : 2.2 to 5.5 V /  $800\mu A$  at 5.5 V

- Low level : 0 to 0.8 V / 20µA at 0.8 V

## MECHANICAL CHARACTERISTICS

Connectors : SMA 2.9 female per MIL-C 39012
Life : 2 million cycles per position

Switching Time\*\*\* : < 40 ms Construction : Splashproof Weight : < 220 g

### **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(\* Average power at 25°C per RF Path)

(\*\* At 25° C ±10%)

(\*\*\* Nominal voltage; 25° C)








SP4T Ramses SMA2.9 40GHz Latching Self-cut-off Auto-reset 12Vdc
TTL Diodes Pins Terminals

SERIE : SPnT PART NUMBER : R573882420


#### **DRAWING**


PAGE **2/2** 




ISSUE **22-03-22** 

TTL input	RF Continuity		
E1 = 1	$IN \leftrightarrow 1$		
E2 = 1	$IN \leftrightarrow 2$		
E3 = 1	IN ↔ 3		
E4 = 1	$IN \leftrightarrow 4$		






# LABEL





# SCHEMATIC DIAGRAM



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.