## **Technical Data Sheet**



SP5T Ramses SMA 18GHz Latching Indicators 12Vdc Diodes Pins Terminals

PAGE 1/2 ISSUE 22-03-22 SERIE : SPnT PART NUMBER : R573432530

### **RF CHARACTERISTICS**

Number of ways : 5

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18
VSWR max	1.20	1.30	1.40	1.50
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB
Isolation min	80 dB	70 dB	60 dB	60 dB
Average power (*)	240 W	150 W	120 W	100 W

### **ELECTRICAL CHARACTERISTICS**

Actuator : LATCHING

Nominal current \*\* : 320 mA / RESET : 1600 mA \*\*\*\*

Actuator voltage (Vcc) : 12V (10.2 to 13V) / NEGATIVE COMMON
Terminals : solder pins (250°C max. / 30 sec.)

Indicator rating : 1 W / 30 V / 100 mA

### MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012
Life : 5 million cycles per position

Switching Time\*\*\* : < 15 msConstruction : Splashproof
Weight : < 220 g

### **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(\* Average power at 25°C per RF Path)

(\*\* At 25° C ±10%)

(\*\*\* Nominal voltage; 25° C)


(\*\*\*\* Reset : supply voltage time 1sec. max. / duty cycle 10%)



# **Technical Data Sheet**



SP5T Ramses SMA 18GHz Latching Indicators 12Vdc Diodes Pins Terminals



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.