Technical Data Sheet



SP10T Ramses SMA 18GHz Latching 28Vdc Positive common D-sub connector

PAGE 1/2 ISSUE 06-02-18 SERIE : SPnT PART NUMBER : R573423015

RF CHARACTERISTICS

Number of ways : 10

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 15.5	15.5 - 18
VSWR max	1.20	1.30	1.40	1.50	1.70
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB	0.70 dB
Isolation min	80 dB	70 dB	60 dB	60 dB	55 dB
Average power (*)	240 W	150 W	120 W	110 W	100 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING

Nominal current ** : 125 mA / RESET : 1250 mA ****

Actuator voltage (Vcc) : 28V (24 to 30V) / POSITIVE COMMON

Terminals : 25 pins D-SUB male connector

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012 Life : 2 million cycles per position

Switching Time*** : < 15 msConstruction : Splashproof
Weight : < 360 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)

(**** Reset : supply voltage time 1sec. max. / duty cycle 10%)




Technical Data Sheet




SP10T Ramses SMA 18GHz Latching 28Vdc Positive common D-sub connector

PAGE 2/2 ISSUE 06-02-18 SERIE : SPnT PART NUMBER : R573423015


DRAWING



Voltage	RF Continuity		
+C -RESET	All ports open		
+C -1	$IN \leftrightarrow 1$		
+C -2	$IN \leftrightarrow 2$		
+C -3	$IN \leftrightarrow 3$		
+C -4	$IN \leftrightarrow 4$		
+C -5	IN ↔ 5		
+C -6	$IN \leftrightarrow 6$		
+C -7	$IN \leftrightarrow 7$		
+C -8	IN ↔ 8		
+C -9	IN ↔ 9		
+C -10	IN ↔ 10		



LABEL




RADIALL® R573423015 0 - 18 GHz Un : 28V Lot : _ _ _

10 1 2

General tolerances . ±0,5 mm [0,02 m

SCHEMATIC DIAGRAM



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.