Technical Data Sheet



SP3T Terminated Ramses SMA 26.5GHz Latching 12Vdc TTL Diodes Pins Terminals

PAGE 1/2 ISSUE 25-11-22 SERIE : SPNT PART NUMBER : R574F22320

RF CHARACTERISTICS

Number of ways : 3

Frequency range : 0 - 26.5 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18	18-26.5
VSWR max	1,20	1,30	1,40	1,50	1,70
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB	0.70 dB
Isolation min	80 dB	70 dB	60 dB	60 dB	50 dB
Average power (*)	240 W	150 W	120 W	100 W	40 W

TERMINATION IMPEDANCE : 50 Ohms

TERM. AVG. POWER AT 25° C : 1 W per termination / 3 W total power

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING

Nominal current ** : 320 mA / RESET : 960 mA ****

Actuator voltage (Vcc) : 12V (10.2 to 13V)

Terminals : solder pins (250°C max. / 30 sec.)

TTL inputs (E) - High level : **2.2 to 5.5 V / 800μA at 5.5 V**

- Low level : 0 to 0.8 V / 20µA at 0.8 V

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012 Life : 3 million cycles per position

Switching Time*** : <15 ms

Construction : Splashproof

Weight : < 250 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)


(**** Reset : supply voltage time 1sec. max. / duty cycle 10%)



Technical Data Sheet



SP3T Terminated Ramses SMA 26.5GHz Latching 12Vdc TTL Diodes Pins Terminals



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.