3SU1500-1AA10-1CA0

Data sheet



holder, 3-way, plastic, 1 NC, screw terminal

product designation product type designation manufacturer's article number of supplied contact module of supplied contact module at position 1 of the supplied holder Actuator design of the actuating element number of contact modules Holder	Plastic
product type designation manufacturer's article number • of supplied contact module • of supplied contact module at position 1 • of the supplied holder Actuator design of the actuating element number of contact modules Holder	3SU1400-1AA10-1CA0 3SU1400-1AA10-1CA0 3SU1500-0AA10-0AA0 3-way with module 1
manufacturer's article number of supplied contact module of supplied contact module at position 1 of the supplied holder Actuator design of the actuating element number of contact modules Holder	3SU1400-1AA10-1CA0 3SU1400-1AA10-1CA0 3SU1500-0AA10-0AA0 3-way with module 1
of supplied contact module of supplied contact module at position 1 of the supplied holder Actuator design of the actuating element number of contact modules Holder	3SU1400-1AA10-1CA0 3SU1500-0AA10-0AA0 3-way with module 1
of supplied contact module at position 1 of the supplied holder Actuator design of the actuating element number of contact modules Holder	3SU1400-1AA10-1CA0 3SU1500-0AA10-0AA0 3-way with module 1
of the supplied holder Actuator design of the actuating element 3 number of contact modules 1 Holder	3SU1500-0AA10-0AA0 3-way with module 1 Plastic
Actuator design of the actuating element number of contact modules Holder	3-way with module 1 Plastic
number of contact modules 1 Holder	1 Plastic
number of contact modules 1 Holder	1 Plastic
material of the holder	
	0
Display	0
number of LED modules 0	
General technical data	
product function positive opening	Yes
product component	
• diode	No
• lamp transformer	No
• light source	No
• series resistor	No
insulation voltage rated value 5	500 V
degree of pollution	3
surge voltage resistance rated value	6 kV
protection class IP of the terminal	IP20
shock resistance	
• acc. to IEC 60068-2-27	Sinusoidal half-wave 50g / 11 ms
• for railway applications acc. to DIN EN 61373	Category 1, Class B
vibration resistance	
• acc. to IEC 60068-2-6	10 500 Hz: 5g
• for railway applications acc. to DIN EN 61373	Category 1, Class B
operating frequency maximum 3	3 600 1/h
mechanical service life (switching cycles) typical	10
thermal current 1	10 A
reference code acc. to IEC 81346-2	U
continuous current of the C characteristic MCB	10 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A

continuous current of the DIAZED fuse link gG	10 A
operating voltage at AC	
— at 50 Hz rated value	5 500 V
— at 60 Hz rated value	5 500 V
	5 500 V
operating voltage at DC rated value Power Electronics	5 500 V
	0 1 (400) (471 (5 4))
contact reliability	One maloperation per 100 million (17 V, 5 mA), one maloperation per 10 million (5 V, 1 mA)
Auxiliary circuit	
design of the contact of auxiliary contacts	Silver alloy
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	0
operational current at AC-15 at 230 V rated value	6 A
Connections/ Terminals	
type of electrical connection	
 of modules and accessories 	Screw-type terminal
type of connectable conductor cross-sections	
 solid with core end processing 	2x (0.5 0.75 mm²)
 solid without core end processing 	2x (1.0 1.5 mm²)
 finely stranded with core end processing 	2x (0.5 1.5 mm²)
 finely stranded without core end processing 	2x (1,0 1,5 mm²)
at AWG cables	2x (18 14)
tightening torque of the screws in the bracket	1 1.2 N·m
• tightening torque with screw-type terminals	0.8 0.9 N·m
Ambient conditions	
 ambient temperature during operation 	-25 +70 °C
ambient temperature during storage	-40 +80 °C
environmental category during operation acc. to IEC 60721	3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 95 %, no condensation in operation permitted)
Installation/ mounting/ dimensions	
fastening method	front panel mounting
 of modules and accessories 	Front plate mounting
height	40 mm
width	30 mm
shape of the installation opening	round
installation width	30 mm
installation depth	49.8 mm
Certificates/ approvals	
One and Decident Assessed	

General Product Approval

Declaration of Conformity











Miscellaneous

Test Certificates

Marine / Shipping

Special Test Certificate Type Test
Certificates/Test
Report









Marine / Shipping

other





Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1500-1AA10-1CA0

Cax online generator


http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1500-1AA10-1CA0


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


https://support.industry.siemens.com/cs/ww/en/ps/3SU1500-1AA10-1CA0


 $Image\ database\ (product\ images,\ 2D\ dimension\ drawings,\ 3D\ models,\ device\ circuit\ diagrams,\ EPLAN\ macros,\ ...)$

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1500-1AA10-1CA0&lang=en









last modified: 8/29/2020 🖸