


# LinearL2™ Power MOSFET w/ Extended FBSOA

## IXTH110N10L2 IXTT110N10L2


$V_{DSS} = 100V$   
 $I_{D25} = 110A$   
 $R_{DS(on)} \leq 18m\Omega$

N-Channel Enhancement Mode  
 Guaranteed FBSOA  
 Avalanche Rated




| Symbol     | Test Conditions   | Maximum Ratings |            |
|------------|---|-----------------|------------|
| $V_{DSS}$  | $T_J = 25^\circ C$ to $150^\circ C$                       | 100             | V          |
| $V_{DGR}$  | $T_J = 25^\circ C$ to $150^\circ C$ , $R_{GS} = 1M\Omega$ | 100             | V          |
| $V_{GSS}$  | Continuous  | $\pm 20$        | V          |
| $V_{GSM}$  | Transient   | $\pm 30$        | V          |
| $I_{D25}$  | $T_C = 25^\circ C$  | 110             | A          |
| $I_{DM}$   | $T_C = 25^\circ C$ , Pulse Width Limited by $T_{JM}$      | 300             | A          |
| $I_A$      | $T_C = 25^\circ C$  | 110             | A          |
| $E_{AS}$   | $T_C = 25^\circ C$  | 3               | J          |
| $P_D$      | $T_C = 25^\circ C$  | 600             | W          |
| $T_J$      |   | -55 to +150     | $^\circ C$ |
| $T_{JM}$   |   | +150            | $^\circ C$ |
| $T_{stg}$  |   | -55 to +150     | $^\circ C$ |
| $T_L$      | 1.6mm (0.063in) from Case for 10s                         | 300             | $^\circ C$ |
| $T_{SOLD}$ | Plastic Body for 10s                                      | 260             | $^\circ C$ |
| $M_d$      | Mounting Torque (TO-247)                                  | 1.13/10         | Nm/lb.in.  |
| Weight     | TO-247  | 6.0             | g          |
|            | TO-268  | 4.0             | g          |

TO-247 (IXTH)



TO-268 (IXTT)



G = Gate      D = Drain  
 S = Source    Tab = Drain

### Features

- Designed for Linear Operation
- International Standard Packages
- Avalanche Rated
- Integrated Gate Resistor for Easy Paralleling
- Guaranteed FBSOA at  $75^\circ C$

### Advantages

- Easy to Mount
- Space Savings
- High Power Density

### Applications

- Solid State Circuit Breakers
- Soft Start Controls
- Linear Amplifiers
- Programmable Loads
- Current Regulators

| Symbol       | Test Conditions<br>( $T_J = 25^\circ C$ , Unless Otherwise Specified) | Characteristic Values |      |               |
|--------------|---|-----------------------|------|---------------|
|              |   | Min.                  | Typ. | Max.          |
| $BV_{DSS}$   | $V_{GS} = 0V$ , $I_D = 250\mu A$                                      | 100                   |      | V             |
| $V_{GS(th)}$ | $V_{DS} = V_{GS}$ , $I_D = 250\mu A$                                  | 2.5                   |      | 4.5 V         |
| $I_{GSS}$    | $V_{GS} = \pm 20V$ , $V_{DS} = 0V$                                    |                       |      | $\pm 100$ nA  |
| $I_{DSS}$    | $V_{DS} = V_{DSS}$ , $V_{GS} = 0V$<br>$T_J = 125^\circ C$             |                       |      | 5 $\mu A$     |
|              |   |                       |      | 50 $\mu A$    |
| $R_{DS(on)}$ | $V_{GS} = 10V$ , $I_D = 0.5 \cdot I_{D25}$ , Note 1                   |                       |      | 18 m $\Omega$ |

| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified)  | Characteristic Values |      |      |                    |
|--------------|--|-----------------------|------|------|--------------------|
|              |  | Min.                  | Typ. | Max. |                    |
| $g_{fs}$     | $V_{DS} = 10\text{V}, I_D = 0.5 \cdot I_{D25}$ , Note 1  | 45                    | 55   | 65   | S                  |
| $C_{iss}$    | $V_{GS} = 0\text{V}, V_{DS} = 25\text{V}, f = 1\text{MHz}$   |                       | 10.5 |      | nF                 |
| $C_{oss}$    |  |                       | 1585 |      | pF                 |
| $C_{rss}$    |  |                       | 420  |      | pF                 |
| $R_{Gi}$     | Gate Input Resistance  |                       | 1.8  |      | $\Omega$           |
| $t_{d(on)}$  | <b>Resistive Switching Times</b><br>$V_{GS} = 10\text{V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 0.5 \cdot I_{D25}$<br>$R_G = 2.2\Omega$ (External) |                       | 28   |      | ns                 |
| $t_r$        |  |                       | 130  |      | ns                 |
| $t_{d(off)}$ |  |                       | 99   |      | ns                 |
| $t_f$        |  |                       | 24   |      | ns                 |
| $Q_{g(on)}$  | $V_{GS} = 10\text{V}, V_{DS} = 0.5 \cdot V_{DSS}, I_D = 0.5 \cdot I_{D25}$   |                       | 260  |      | nC                 |
| $Q_{gs}$     |  |                       | 52   |      | nC                 |
| $Q_{gd}$     |  |                       | 106  |      | nC                 |
| $R_{thJC}$   | TO-247   |                       |      | 0.21 | $^\circ\text{C/W}$ |
| $R_{thCS}$   |  |                       | 0.21 |      | $^\circ\text{C/W}$ |

### Safe Operating Area Specification

| Symbol | Test Conditions   | Characteristic Values |      |      |   |
|--------|---|-----------------------|------|------|---|
|        |   | Min.                  | Typ. | Max. |   |
| SOA    | $V_{DS} = 80\text{V}, I_D = 3.6\text{A}, T_C = 75^\circ\text{C}, t_p = 5\text{s}$ | 360                   |      |      | W |

### Source-Drain Diode

| Symbol   | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , Unless Otherwise Specified)                     | Characteristic Values |      |      |               |
|----------|---|-----------------------|------|------|---------------|
|          |   | Min.                  | Typ. | Max. |               |
| $I_S$    | $V_{GS} = 0\text{V}$  |                       |      | 110  | A             |
| $I_{SM}$ | Repetitive, Pulse Width Limited by $T_{JM}$   |                       |      | 440  | A             |
| $V_{SD}$ | $I_F = I_S, V_{GS} = 0\text{V}$ , Note 1  |                       |      | 1.4  | V             |
| $t_{rr}$ | $I_F = 55\text{A}, -di/dt = 100\text{A}/\mu\text{s},$<br>$V_R = 50\text{V}, V_{GS} = 0\text{V}$ |                       | 230  |      | ns            |
| $I_{RM}$ |   |                       | 19.4 |      | A             |
| $Q_{RM}$ |   |                       | 2.2  |      | $\mu\text{C}$ |

Note 1. Pulse test,  $t \leq 300\mu\text{s}$ ; duty cycle,  $d \leq 2\%$ .


### ADVANCE TECHNICAL INFORMATION

The product presented herein is under development. The Technical Specifications offered are derived from a subjective evaluation of the design, based upon prior knowledge and experience, and constitute a "considered reflection" of the anticipated result. IXYS reserves the right to change limits, test conditions, and dimensions without notice.

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered 4,835,592 4,931,844 5,049,961 5,237,481 6,162,665 6,404,065 B1 6,683,344 6,727,585 7,005,734 B2 7,157,338B2  
by one or more of the following U.S. patents: 4,850,072 5,017,508 5,063,307 5,381,025 6,259,123 B1 6,534,343 6,710,405 B2 6,759,692 7,063,975 B2  
4,881,106 5,034,796 5,187,117 5,486,715 6,306,728 B1 6,583,505 6,710,463 6,771,478 B2 7,071,537


### TO-247 (IXTH) Outline



Terminals: 1 - Gate 2 - Drain  
3 - Source Tab - Drain

| Dim.           | Millimeter |       | Inches |       |
|----------------|------------|-------|--------|-------|
|                | Min.       | Max.  | Min.   | Max.  |
| A              | 4.7        | 5.3   | .185   | .209  |
| A <sub>1</sub> | 2.2        | 2.54  | .087   | .102  |
| A <sub>2</sub> | 2.2        | 2.6   | .059   | .098  |
| b              | 1.0        | 1.4   | .040   | .055  |
| b <sub>1</sub> | 1.65       | 2.13  | .065   | .084  |
| b <sub>2</sub> | 2.87       | 3.12  | .113   | .123  |
| C              | .4         | .8    | .016   | .031  |
| D              | 20.80      | 21.46 | .819   | .845  |
| E              | 15.75      | 16.26 | .610   | .640  |
| e              | 5.20       | 5.72  | 0.205  | 0.225 |
| L              | 19.81      | 20.32 | .780   | .800  |
| L <sub>1</sub> |            | 4.50  |        | .177  |
| ∅P             | 3.55       | 3.65  | .140   | .144  |
| Q              | 5.89       | 6.40  | 0.232  | 0.252 |
| R              | 4.32       | 5.49  | .170   | .216  |
| S              | 6.15       | BSC   | 242    | BSC   |

### TO-268 (IXTT) Outline



Terminals: 1 - Gate 2 - Drain  
3 - Source Tab - Drain

| SYM            | INCHES |          | MILLIMETERS |          |
|----------------|--------|----------|-------------|----------|
|                | MIN    | MAX      | MIN         | MAX      |
| A              | .193   | .201     | 4.90        | 5.10     |
| A <sub>1</sub> | .106   | .114     | 2.70        | 2.90     |
| A <sub>2</sub> | .001   | .010     | 0.02        | 0.25     |
| b              | .045   | .057     | 1.15        | 1.45     |
| b <sub>2</sub> | .075   | .083     | 1.90        | 2.10     |
| C              | .016   | .026     | 0.40        | 0.65     |
| C <sub>2</sub> | .057   | .063     | 1.45        | 1.60     |
| D              | .543   | .551     | 13.80       | 14.00    |
| D <sub>1</sub> | .488   | .500     | 12.40       | 12.70    |
| E              | .624   | .632     | 15.85       | 16.05    |
| E <sub>1</sub> | .524   | .535     | 13.30       | 13.60    |
| e              |        | .215 BSC |             | 5.45 BSC |
| H              | .736   | .752     | 18.70       | 19.10    |
| L              | .094   | .106     | 2.40        | 2.70     |
| L <sub>1</sub> | .047   | .055     | 1.20        | 1.40     |
| L <sub>2</sub> | .039   | .045     | 1.00        | 1.15     |
| L <sub>3</sub> |        | .010 BSC |             | 0.25 BSC |
| L <sub>4</sub> | .150   | .161     | 3.80        | 4.10     |

Fig. 1. Output Characteristics @  $T_J = 25^\circ\text{C}$




Fig. 2. Extended Output Characteristics @  $T_J = 25^\circ\text{C}$




Fig. 3. Output Characteristics @  $T_J = 125^\circ\text{C}$




Fig. 4.  $R_{DS(on)}$  Normalized to  $I_D = 55\text{A}$  Value vs. Junction Temperature




Fig. 5.  $R_{DS(on)}$  Normalized to  $I_D = 55\text{A}$  Value vs. Drain Current







Fig. 6. Maximum Drain Current vs. Case Temperature




**Fig. 7. Input Admittance**




**Fig. 8. Transconductance**




**Fig. 9. Forward Voltage Drop of Intrinsic Diode**




**Fig. 10. Gate Charge**




**Fig. 11. Capacitance**




**Fig. 12. Maximum Transient Thermal Impedance**



**Fig. 13. Forward-Bias Safe Operating Area**  
@  $T_C = 25^\circ\text{C}$



**Fig. 14. Forward-Bias Safe Operating Area**  
@  $T_C = 75^\circ\text{C}$





---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).