

Multilayer Ceramic Chip Capacitor

NOVACA	NOVACAP + SYFER + VOLTRONICS						
Part Number:	2211JA250102J	KTSYX	Description:	2211 250Vac (Y2), 305Vac (X1), 50/60Hz / 1000Vdc 1.0nF ±5% C0G/NP0 (1B) to AEC- Q200			
Approval	IEC/EN60384-14:2013+A	1		*			
Specifications:				12			
			<	Ŧ			
Certification:	TÜV R60153659 / ID1111	233476		T			
	UL/cUL E228790-20201127			+ 3			
			<				
Classification:	IEC/EN 60384-14:2013+A	1 Class Y2 / X1		m L4			
	UL/cUL FOWX2, FOWX8			L2 L4 L3			
			Component				
			Component Marking and Certification Bodies:				
Material Group I : CTI >= 600			SY10	02 C C C S C C C C C C C C C C C C C C C			
Mechanical Specification							
Size Code			2211				
Length (L1) in mm (")			5.7 ± 0.40 (0.225 ± 0.016)				
Width (W) in mm (")			2.79 ± 0.30 (0.11 ± 0.012)				
Thickness (T) in mm	(")		2.80 Max (0.11 Max)				
Minimum Terminatior	n Band (L2,L3) in mm (")		0.50 (0.020)				
Maximum Terminatio	n Band (L2,L3) in mm (")		0.80 (0.030)				
Minimum Band Gap (Minimum Band Gap (L4) in mm (")			4.0 (0.158)			
Termination Material			Nickel Barrier, Sn Plated Solder (RoHS compliant)				
Solderability			IEC-60068-2-58				
Packaging	-			7" Reel Horizontal Orientation, 500 per reel			
General Electrical Specification							
Rated Voltage			Class Y2 (250Vac), Class X1 (305Vac), 50/60Hz, 5kV impulse				
Humidity Grade	Humidity Grade			Grade III (IEC/EN60384-14:2013 Annex 1)			
Maximum DC Working Voltage			1000Vdc certified / (2500Vdc outside scope of any specification)				
Nominal Capacitance Value			1.0nF				
Capacitance Tolerand	се		±5%				
Tangent of Loss Angle (Tan δ)			≤0.0015				
Capacitance and Tan δ Test Conditions			1.0Vrms @ 1MHz				
Voltage Proof			100% test: 4000Vdc 1s min / 5s max				
(50mA max charging current for DC tests)		AQL test: 4000Vdc / 3000Vac 60s min / 5kV 1.2x50µs impulse					
Min Insulation Resistance (IR) Dielectric Classification			100.00GOhm @ 100Vdc C0G/NP0 (1B) to AEC-Q200				
			-55°C / +125°C				
Rated Temperature Range			-55 C / +125 C No DC Voltage 0±30ppm/°C				
Maximum Capacitance Change over Temperature Range			•	Rated DC Voltage -			
Climatic Category (IEC)			55/125/56				
Ageing Characteristic			Zero				
Knowles Precisi	ion Devices - Sales	This datasheet is for a	standard item and is confi	med valid on the date generated, the latest published data			
Europe: KPD-Europ	pe-sales@knowles.com	This datasheet is for a standard item and is confirmed valid on the date generated, the latest published da for this part may differ and is available at http://www.knowlescapacitors.com or by contacting us.					
Asia: KPD-Asia-sales@knowles.com		ined on this drawing is Data is correct to the best of our knowledge, errors and omissions excepted.					
USA: KPD-NA-sales@knowles.com any form or disclose		any form or disclosed to a t	be copied in whole or part in third party without the consent	·			
www.knowlescapacitors.com of Knowles and a specification.			tomer mentioned within this	Date: Thursday, September 02, 2021 20210902 210554394UTC			



Multilayer Ceramic Chip Capacitor

NOVACAP + SYFER + VOLTRONICS							
Part Number: 2211JA250102J	IKTSYX	Description:	2211 250Vac (Y2), 305Vac (X1), 50/60Hz / 1000Vdc 1.0nF ±5% C0G/NP0 (1B) to AEC- Q200				
Environmental							
RoHS Compliant to 2011/65/EC as amende	ed by 2015/863/EU	Compliant					
REACH Compliant		211 compliant					
California Proposition 65		No exposure risk					
Board Layout							
Knowles' conventional 2-terminal chip generally be mounted using pad designs i international specification IPC-7351, Gen for Surface Mount Design and Land Patte there are some other factors that have bee mechanical stress, such as reducing the than the chip width. In addition, the position board should be considered. Some high voltage parts may require m board layout and/or the addition of a co prevent flashover. Refer to application further information.	n accordance with eric Requirements ern Standards, but n shown to reduce pad width to less n of the chip on the odifications to the nformal coating to		IPC-7351 pad design 2211 C 5.40mm 0.213" Y 1.35mm 0.053" X 3.10mm 0.122" 1 1 1 2 1 1 1 1 1 1 1 1				
Packaging							
Tape packaging information for tape-ar Tape and reel packing of surface mour capacitors for automatic placement are with IEC60286-3.	ting chip		Product identifying label Plastic carrier tape Top tape 8 or 12mm 178mm (7") or nominal 330mm (13") dia. reel				
Soldering							
Reflow solder in accordance with IPC-, Recommended reflow profile as laid do IPC/JEDEC J-STD-020. Wave soldering is also possible, but ca taken for case sizes 1210 and larger a thickness >1.0mm. Trials are encourage Hand soldering is not recommended as component damage through thermal signature.	own in are must be nd component ged. nd can lead to	Temperature	Max Min t ts Time				
Application notes with mounting and handling guidance are available on request.							
Compex DLI .	Johanson MFG	Novacap	Syfer Voltronics				
Knowles Precision Devices - Sales Europe: KPD-Europe-sales@knowles.com Asia: KPD-Asia-sales@knowles.com USA: KPD-NA-sales@knowles.com www.knowlescapacitors.com							