



Click [here](#) for the 3D model.

Dimensions	
L	30.5mm MAX
H	17mm MAX
T	10.5mm MAX
S	25.4mm +/-0.4mm
LL	30mm +5mm
F	1mm NOM

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	100

General Information	
Series	PME264/P264
Dielectric	Metallized Paper
Style	Radial
Features	EMI Safety
RoHS	Yes
Lead	Wire Leads
Safety Class	X2
Qualifications	ENEC, UL, cUL
AEC-Q200	No
THB Performance	No
Construction	Molded
Typical Component Weight	7.65 g

Specifications	
Capacitance	0.047 uF
Capacitance Tolerance	20%
Voltage AC	660 VAC (X2)
Voltage DC	1500 VDC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Dissipation Factor	1.3% 1kHz
Insulation Resistance	12 GOhms
Max dV/dt	1000 V/us