Technical Data Sheet



DPDT Ramses SMA 18GHz Latching Indicators 12Vdc Positive common

Pins Terminals

PAGE 1/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577442012

RF CHARACTERISTICS

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18
VSWR max	1.20	1.30	1.40	1.50
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB
Isolation min	80 dB	70 dB	65 dB	60 dB
Average power (*)	240 W	150 W	120 W	100 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING
Nominal current ** : 320 mA

Actuator voltage (Vcc) : 12V (10.2 to 13V) / POSITIVE COMMON Terminals : solder pins (250°C max. / 30 sec.)

Indicator rating : 1 W / 30 V / 100 mA

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 2.5 million cycles

Switching Time*** : <15 ms

Construction : Splashproof

Weight : <100 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)




Technical Data Sheet



DPDT Ramses SMA 18GHz Latching Indicators 12Vdc Positive common


Pins Terminals



General tolerances : ±0,5 mm [0,02 in]

000

SCHEMATIC DIAGRAM



Voltage	RF Continuity	Ind.
+C -1	$1 \leftrightarrow 3 \ / \ 2 \leftrightarrow 4$	C.1
+C -2	$1 \leftrightarrow 2 / 3 \leftrightarrow 4$	C.2