Technical Data Sheet



DPDT Ramses SMA2.9 40GHz Latching Indicators 28Vdc Diodes Pins

Terminals with bracket

PAGE 1/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577843030

RF CHARACTERISTICS

Frequency range : 0 - 40 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 6	6 - 12.4	12.4 - 18	18 - 26.5	26.5 - 40
VSWR max	1.30	1.40	1.50	1.70	1.90
Insertion loss max	0.30 dB	0.40 dB	0.50 dB	0.70 dB	0.80 dB
Isolation min	70 dB	60 dB	60 dB	55 dB	50 dB
Average power (*)	80 W	60 W	50 W	20 W	10 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING
Nominal current ** : 125 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / NEGATIVE COMMON
Terminals : solder pins (250°C max. / 30 sec.)

Indicator rating : 1 W / 30 V / 100 mA

MECHANICAL CHARACTERISTICS

Connectors : SMA 2.9 female per MIL-C 39012

Life : 2.5 million cycles

Switching Time*** : < 15 msConstruction : Splashproof
Weight : < 100 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)










DPDT Ramses SMA2.9 40GHz Latching Indicators 28Vdc Diodes Pins
Terminals with bracket

PAGE 2/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577843030

DRAWING








General tolerances: ±0,5 mm [0,02 in]

SCHEMATIC DIAGRAM





LABEL

Voltage RF Continuity Ind.

-C +1 $1 \leftrightarrow 3 / 2 \leftrightarrow 4$ C.1

-C +2 $1 \leftrightarrow 2 / 3 \leftrightarrow 4$ C.2