



DPDT Ramses SMA2.9 40GHz Latching Self-cut-off Indicators 28Vdc
Diodes D-sub connector with bracket

PAGE 1/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577863005

RF CHARACTERISTICS

Frequency range : 0 - 40 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 6	6 - 12.4	12.4 - 18	18 - 26.5	26.5 - 40
VSWR max	1.30	1.40	1.50	1.70	1.90
Insertion loss max	0.30 dB	0.40 dB	0.50 dB	0.70 dB	0.80 dB
Isolation min	70 dB	60 dB	60 dB	55 dB	50 dB
Average power (*)	80 W	60 W	50 W	20 W	10 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING
Nominal current ** : 125 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / NEGATIVE COMMON

Terminals : 9 pins D-SUB male connector

Indicator rating : 1 W / 30 V / 100 mA
Self cut-off time : 40 ms < CT < 120 ms

MECHANICAL CHARACTERISTICS

Connectors : SMA 2.9 female per MIL-C 39012

Life : 2.5 million cycles

Switching Time*** : < 15 ms

Construction : Splashproof

Weight : < 100 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)









DPDT Ramses SMA2.9 40GHz Latching Self-cut-off Indicators 28Vdc Diodes D-sub connector with bracket

PAGE **2/2** ISSUE **22-03-22** SERIE: DPDT PART NUMBER: **R577863005**


DRAWING








LABEL




RADIALL® R577863005 0 - 40 GHz Un: 28V Lot : _ _ _ _



General tolerances: ±0,5 mm [0,02 in]

SCHEMATIC DIAGRAM



Voltage	RF Continuity	Ind.
-C +1	$1 \leftrightarrow 3 / 2 \leftrightarrow 4$	C.1
-C +2	$1 \leftrightarrow 2 / 3 \leftrightarrow 4$	C.2