



SPDT Terminated Ramses SMA 26.5GHz Latching Indicators 12Vdc Internal loads Pins terminals

PAGE 1/2 ISSUE 09-03-21 SERIE : SPDT ZC PART NUMBER : R585F42200

#### **RF CHARACTERISTICS**

Frequency range : 0 - 26.5 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18	18 - 26.5
VSWR max	1.20	1.30	1.40	1.50	1.70
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB	0.70 dB
Isolation min	80 dB	70 dB	60 dB	60 dB	55 dB
Average power (*)	240 W	150 W	120 W	100 W	40 W

#### **ELECTRICAL CHARACTERISTICS**

Actuator : LATCHING
Nominal current \*\* : 420 mA

Actuator voltage (Vcc) : 12V (10.2 to 13V) / NEGATIVE COMMON Terminals : solder pins (250°C max. / 30 sec.)

Indicator rating : 1 W / 30 V / 100 mA

# MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 2 million cycles

### **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(\* Average power at 25°C per RF Path)

(\*\* At 25° C ±10%)

(\*\*\* Nominal voltage; 25° C)



# **Technical Data Sheet**



SPDT Terminated Ramses SMA 26.5GHz Latching Indicators 12Vdc Internal loads Pins terminals

