Technical Data Sheet



SP3T Ramses SMA2.9 40GHz Normally open 12Vdc BCD TTL Diodes D-sub connector

PAGE 1/2 ISSUE 22-03-22 SERIE: SPnT PART NUMBER: R573802385

RF CHARACTERISTICS

Number of ways : 3

Frequency range : 0 - 40 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 6	6 - 12.4	12.4 - 18	18 - 26.5	26.5 - 40
VSWR max	1.30	1.40	1.50	1.70	2.20
Insertion loss max	0.20 dB	0.40 dB	0.50 dB	0.70 dB	1.10 dB
Isolation min	70 dB	60 dB	60 dB	55 dB	50 dB
Average power (*)	40 W	30 W	25 W	15 W	5 W

ELECTRICAL CHARACTERISTICS

Actuator : NORMALLY OPEN

Nominal current ** : 250 mA

Actuator voltage (Vcc) : 12V (10.2 to 13V)

Terminals : 25 pins D-SUB male connector BCD inputs (E) - High level : 3.5 to 5.5 V / 800µA at 5.5 V

- Low level : 0 to 1.5 V / 20µA at 0.8 V

MECHANICAL CHARACTERISTICS

Connectors : SMA 2.9 female per MIL-C 39012
Life : 2 million cycles per position

Switching Time*** : <15 ms

Construction : Splashproof

Weight : < 220 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)




Technical Data Sheet




SP3T Ramses SMA2.9 40GHz Normally open 12Vdc BCD TTL Diodes D-sub connector

PAGE 2/2 | ISSUE 22-03-22 | SERIE : SPnT | PART NUMBER : R573802385


DRAWING



BCD TRUTH TABLE				
E3	E2	E1	RF continuity	
0	0	0	Last Position	
1	1	1	All ports open	
0	0	1	IN ↔ 1	
0	1	0	$IN \leftrightarrow 2$	
0	1	1	$IN \leftrightarrow 3$	




LABEL





SCHEMATIC DIAGRAM



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.