



SPDT Terminated Ramses SMA 18GHz Latching Self-cut-off 12Vdc
Positive common Diodes Internal loads Pins terminals

PAGE 1/2 ISSUE 09-03-21 SERIE : SPDT ZC PART NUMBER : R585452210

### **RF CHARACTERISTICS**

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18
VSWR max	1.20	1.30	1.40	1.50
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB
Isolation min	80 dB	70 dB	60 dB	60 dB
Average power (*)	240 W	150 W	120 W	100 W

### **ELECTRICAL CHARACTERISTICS**

Actuator : LATCHING
Nominal current \*\* : 420 mA

Actuator voltage (Vcc) : 12V (10.2 to 13V) / POSITIVE COMMON Terminals : solder pins (250°C max. / 30 sec.)

Self cut-off time : 40 ms < CT < 120 ms

# MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 2 million cycles

Switching Time\*\*\* : < 10 ms

Construction : Splashproof

Weight : < 100 g

# ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(\* Average power at 25°C per RF Path)

(\*\* At 25° C ±10%)

(\*\*\* Nominal voltage; 25° C)








SPDT Terminated Ramses SMA 18GHz Latching Self-cut-off 12Vdc
Positive common Diodes Internal loads Pins terminals


PAGE 2/2 ISSUE 09-03-21 SERIE: SPDT ZC PART NUMBER: R585452210

# DRAWING [2.189] 55.6 [0.44] [0.44]

11.18



11.18






General tolerances: ±0,5 mm [0,02 in]

## SCHEMATIC DIAGRAM

RF input



Voltage	RF Continuity	
+C -1	C↔1 / 2↔50Ω	
+C -2	C↔2 / 1↔50Ω	