



SPDT Terminated Ramses SMA 18GHz Latching Indicators 28Vdc Positive common Diodes Internal loads Pins terminals

PAGE 1/2 ISSUE 09-03-21 SERIE : SPDT ZC PART NUMBER : R585443240

RF CHARACTERISTICS

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18
VSWR max	1.20	1.30	1.40	1.50
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB
Isolation min	80 dB	70 dB	60 dB	60 dB
Average power (*)	240 W	150 W	120 W	100 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING
Nominal current ** : 160 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / POSITIVE COMMON Terminals : solder pins (250°C max. / 30 sec.)

Indicator rating : 1 W / 30 V / 100 mA

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 2 million cycles

Switching Time*** : < 10 ms

Construction : Splashproof

Weight : < 100 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)







SPDT Terminated Ramses SMA 18GHz Latching Indicators 28Vdc Positive common Diodes Internal loads Pins terminals

PAGE **2/2** ISSUE **09-03-21** SERIE: SPDT ZC PART NUMBER: **R585443240 DRAWING** [2.189] 55.6 0.44 0.44 11.18 11.18 [0.138 min.] LABEL 3.5 min. •C 0 - 18 GHz Un: 28V **RADIALL®** R585443240 Lot : _ _ _ _ [0.122][0.094]С 1 4 x ¯ Ø 3.1 [0.059 max.] 1.5 max. [0.303 max.] 7 7 max [0.441] 11.2 [1.321] 33.55 **@@@ %** 00 0 General tolerances: ±0,5 mm [0,02 in] **SCHEMATIC DIAGRAM** Indicator terminals RF input -01 -02 50Ω Termination -O C Actuator RF Continuity Voltage Ind. ₹W0 С +C C↔1 / 2↔50Ω 0-1 +C -2 $C\leftrightarrow 2/1\leftrightarrow 50\Omega$ **4**0+C -0-5 Power input terminals ∞ \$W0-0 50Ω Termination