

## **Technical Data Sheet**


DPDT Ramses N 3GHz Latching 28Vdc Pins Terminals

	HARACTERI							
	Frequency r Impedance	ange			0 - 3 GHz 50 Ohms			
	Frequency (	GHz)	DC - 1	1 - 2	2 - 3			
	VSWR max		1.15	1.20	1.25			
	Insertion los		0.15 dB	0.20 dB	0.25 dB			
	Isolation min		85 dB 700 W	80 dB 500 W	75 dB 400 W			
<u>ELE(</u>	Actuator Nominal cur Actuator vol Terminals	rent **	<u>FICS</u>	:	-	0V) / NEGATIVE C( (250°C max. / 30 se		
MEC	HANICAL CH	ARACTERIS	<u>STICS</u>					
	Connectors			:	N female pe	r MIL-C 39012		
	Life				2.5 million o	cycles		
	Switching Ti Construction				< 15 ms Splashproo	f		
	Weight	1			< 215 g	•		
ENV	IRONMENTA	_ CHARACT	ERISTICS					
	Operating te	mperature ra	ange	:	-40°C to +85	5°C		
		perature ran	-	:	-55°C to +85	5°C	R	oHS
(* (** (***	At 25° C ±10	ver at 25°C p 0%) :age ; 25° C)	er RF Path)				· COM	PLIAN



## **Technical Data Sheet**

DPDT Ramses N 3GHz Latching 28Vdc Pins Terminals



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.