


Technical Data Sheet

SP6T Terminated Ramses SMA2.9 40GHz Normally open 28Vdc Positive common Diodes Pins Terminals

PAGE 1/2	PAGE 1/2 ISSUE 26-01-17		SERIE : SPnT		PART NUMBER : R574803640			
RF CHARACTERI	<u>STICS</u>							
Number of ways Frequency range Impedance			:6 :0 - 40 GHz :50 Ohms					
Frequency ((GHz)	DC - 6	6 - 12.4	12.4 - 18	18 - 26.5	26.5 - 40]	
VSWR max		1.30	1.40	1.50	1.70	2.20		
Insertion loss max).20 dB	0.40 dB	0.50 dB	0.70 dB	1.10 dB		
Isolation min		70 dB	60 dB	60 dB	55 dB	50 dB		
Average po	wer (*)	40 W	30 W	25 W	15 W	5 W		
	TERMINATION IMPEDANCE: 50 OhmsTERM. AVG. POWER AT 25° C: 1 W per termination / 3 W total power							
ELECTRICAL CH	ARACTERISTICS	<u>6</u>						
Actuator			: NORMALLY OPEN : 102 mA					
Nominal current ** Actuator voltage (Vcc)			2 28V (24 to 30V) / POSITIVE COMMON					
Terminals			: solder pins (250°C max. / 30 sec.)					
MECHANICAL CHARACTERISTICS Connectors Life Switching Time*** Construction Weight			 SMA 2.9 female per MIL-C 39012 2 million cycles per position < 15 ms Splashproof < 250 g 					
<u>ENVIRONMENTA</u>	L CHARACTERI	<u>STICS</u>						
	Operating temperature range Storage temperature range			: -40°C to +85°C : -55°C to +85°C			ROHS	
(** At 25° C ±1	wer at 25°C per F 0%) tage ; 25° C)	RF Path)					· COMPLIAN	

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.