



DPDT Ramses SMA2.9 40GHz Latching 28Vdc Positive common Diodes
Pins Terminals with bracket

PAGE 1/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577833040

## **RF CHARACTERISTICS**

Frequency range : 0 - 40 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 6	6 - 12.4	12.4 - 18	18 - 26.5	26.5 - 40
VSWR max	1.30	1.40	1.50	1.70	1.90
Insertion loss max	0.30 dB	0.40 dB	0.50 dB	0.70 dB	0.80 dB
Isolation min	70 dB	60 dB	60 dB	55 dB	50 dB
Average power (*)	80 W	60 W	50 W	20 W	10 W

## **ELECTRICAL CHARACTERISTICS**

Actuator : LATCHING
Nominal current \*\* : 125 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / POSITIVE COMMON Terminals : solder pins (250°C max. / 30 sec.)

## MECHANICAL CHARACTERISTICS

Connectors : SMA 2.9 female per MIL-C 39012

Life : 2.5 million cycles

Switching Time\*\*\* : <15 ms

Construction : Splashproof

Weight : <100 g

# **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(\* Average power at 25°C per RF Path)

(\*\* At 25° C ±10%)

(\*\*\* Nominal voltage; 25° C)










DPDT Ramses SMA2.9 40GHz Latching 28Vdc Positive common Diodes
Pins Terminals with bracket

PAGE 2/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577833040

#### **DRAWING**








General tolerances: ±0,5 mm [0,02 in]

# SCHEMATIC DIAGRAM





# LABEL

-1 -2 +C

RADIALL®

R577833040
0 - 40 GHz
Un : 28V
Lot : \_ \_ \_

Voltage	RF Continuity		
+C -1	$1 \leftrightarrow 3 / 2 \leftrightarrow 4$		
+C -2	$1 \leftrightarrow 2 / 3 \leftrightarrow 4$		