

# soberton inc.

# **SP DYNAMIC SPEAKER UNIT**

**Acoustic Product Specification** 

**Product Number: SP-1504-17** 



Release | Revision: A/2018

### **CONTENTS**

This document contains the technical specifications for the dynamic speaker unit.

# Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

# Page 2

**Reliability Tests** 

#### Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

#### Page 4

Frequency Response Curve

#### Page 5

**Dimensions** 

#### Page 6

**Packing** 

# **Dynamic Speaker Electroacoustic Characteristics**

#### **Sound Pressure Level**

93±3dB SPL @0.8, 1.0, 1.5 and 2.0KHz in average (0dB SPL=20μPa) Measuring Condition: 0.5W (Sine wave) 10cm measured with baffler shown in Fig.1

#### **Frequency Response Curve**

As shown in Figure 2

#### **Response Frequency**

1000±20%Hz @ 1V (without baffler)

#### **Input Power (Nominal and Maximum)**

Rated Noise Power 0.5W

Short Term Max Power: 0.8W must be normal at a white noise (1W, F0 ~ 20KHz) for one minute

## **Operation Test**

Must be free audible noise (buzzes and rattles)

(300 ~ 8KHz frequency range, input level up to 2.0Vrms)

#### **Distortion**

Less than 10% @1KHz,0.1M, 0.1W, frequency range, input level up to 2.0Vrms

# **General Specifications**

# **Operating Temperature Range**

-20°C~+60°C

# **Storage Temperature Range**

-30°C~+70°C

# **Standard Test Conditions**

Temperature 17°C~25°C

Relative Humidity 45%~80%(RH)

#### **AC Impedance**

 $8\pm15\%\Omega$  (@2KHz 1V) without baffler

### **Dimension**

Ø15.0x3.9mm WIRE 40mm UL1571/AWG32#

#### **IP Level**

**IP50** 



# soberton inc.

# SP DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

**Product Number: SP-1504-17** 



# Release | Revision: A/2018

### **CONTENTS**

This document contains the technical specifications for the dynamic speaker unit.

# Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

# Page 2

**Reliability Tests** 

#### Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

## Page 4

Frequency Response Curve

#### Page 5

Dimensions

#### Page 6

**Packing** 

# **Reliability Tests**

The sound pressure as specified will neither deviate more than ±3dB from the initial value, nor have any significant damage after any of following testing.

#### **High Temperature Test**

High Temperature +60±2°C

**Duration** 96 hours

#### **Low Temperature Test**

**Low Temperature** -20±2°C

**Duration** 96 hours

#### **Heat Shock Test**

High Temperature +60±2°C

Low Temperature -20±2°C

Changeover Time < 30 seconds

**Duration** 1 hour

Cycle 100

## **Humidity Test**

Temperature + 40±2°C

**Relative Humidity** 90%~95%

**Duration** 96 hours

# **Temperature Cycle Test**

Temperature -20°C +60°C

**Duration** 45 minutes 45 minutes

Temperature gradient 1~3°C/min

Cycle 25

# **Drop Test**

Mounted with dummy set mass  $100\,\mathrm{g}$ 

Height 1.5 m

Cycle 6 (1 each plain) onto the concrete board

#### **Load Test**

Speaker mode: White Noise (EIA filter) for 96 hours@0.5W input power



# SP DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

Product Number: SP-1504-17



# Release | Revision: A/2018

### **CONTENTS**

This document contains the technical specifications for the dynamic speaker unit.

# Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

# Page 2

**Reliability Tests** 

# Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

## Page 4

Frequency Response Curve

# Page 5

Dimensions

#### Page 6

**Packing** 

# Measuring Method (Speaker Mode)

#### **Standard Test Condition**

Temperature 15 ~ 35°C

Relative humidity 45% ~ 85%

Atmospheric pressure 860mbar to 1060mbar

#### **Standard Test Fixture**

Input Power 0.5W (2.0V)


Zero Level -dB

Mode TSR

Potentiometer Range 50dB

Sweep Time 0.5sec

# **Standard Test Condition of Speaker (Fig. 1)**





# SP DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

**Product Number: SP-1504-17** 



Release | Revision: A/2018

# **CONTENTS**

This document contains the technical specifications for the dynamic speaker unit.

# Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

# Page 2

**Reliability Tests** 

# Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

## Page 4

Frequency Response Curve


# Page 5

Dimensions

#### Page 6

Packing

# Frequency Response Curve (Fig. 2)





# soberton inc.

# SP DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

**Product Number: SP-1504-17** 



Release | Revision: A/2018

# CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

# Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

# Page 2

**Reliability Tests** 

# Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

#### Page 4

Frequency Response Curve

# Page 5


Dimensions


## Page 6

Packing

# **Dimensions**

Tolerance: ±0.5 (unit: mm)





No.	Part Name	Material	Quantity
1	Wire (40mm)	UL1571 AWG32#	2
2	PCB	0.4 Tinned PCB	1
3	Frame	PBT	1
4	Magnet	NdFeB-N42	1
5	Plate	SPCC	1
6	Voice Coil	Copper	1
7	Membrane	PEN	1
8	Сар	SUS304	1
9	Screen Gasket	0.4 Single-sided cloth	1
10	Damping Net	180Mesh	1



# SP DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

Product Number: SP-1504-17



Release | Revision: A/2018

# **CONTENTS**

This document contains the technical specifications for the dynamic speaker unit.

# Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

# Page 2

**Reliability Tests** 

# Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

## Page 4

Frequency Response Curve


#### Page 5


Dimensions

#### Page 6

**Packing** 

# 100PCS×10=1000PCS





1000PCS×5=5000PCS

