

# **SP DYNAMIC SPEAKER UNIT**

**Acoustic Product Specification** 

**Product Number: SP-1605-5** 



Release | Revision: C/2018

#### **CONTENTS**

This document contains the technical specifications for the dynamic speaker unit.

# Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

# Page 2

**Reliability Tests** 

### Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

#### Page 4

Frequency Response Curve

#### Page 5

**Dimensions** 

#### Page 6

**Packing** 

# **Dynamic Speaker Electroacoustic Characteristics**

#### **Sound Pressure Level**

 $88\pm3dB\ SPL\ @0.8,\ 1.0,\ 1.5\ and\ 2.0\ KHz\ in\ average\ (0dB\ SPL=20\mu Pa)$ Measuring Condition: 0.1W (Sine wave) 10cm measured with baffler shown in Fig.1.

#### **Frequency Response Curve**

As shown in Figure 2

#### **Response Frequency**

1000±20%Hz @ 1V. (Without Baffler)

#### **Input Power (Nominal and Maximum)**

Rated Noise Power 0.5W

**Short Term Max Power:** 0.8W must be normal at a white noise (1W, F0 ~ 20KHz) for one minute

#### **Operation Test**

Must be free audible noise (buzzes and rattles)

(300 ~ 8KHz frequency range, input level up to 2.0 Vrms)

#### **Distortion**

Less than 10% @1KHz, 0.1M, 0.1W frequency range, input level up to 2.0 Vrms

# **General Specifications**

# **Operating Temperature Range**

-20°C~+60°C

# **Storage Temperature Range**

-25°C~+70°C

## **Standard Test Conditions**

Temperature 17°C~25°C

Relative Humidity 45%~80%(RH)

#### **AC** Impedance

 $8\pm15\%\Omega$  (@2KHz 1V) without baffler

#### **Dimension**

Ø16.0x4.7mm WIRE 38mm

#### **IP Level**

**IP50** 



# **SP DYNAMIC SPEAKER UNIT**

**Acoustic Product Specification** 

**Product Number: SP-1605-5** 



Release | Revision: C/2018

## **CONTENTS**

This document contains the technical specifications for the dynamic speaker unit.

# Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

# Page 2

**Reliability Tests** 

### Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

## Page 4

Frequency Response Curve

# Page 5

**Dimensions** 

#### Page 6

**Packing** 

# **Reliability Tests**

The sound pressure as specified will neither deviate more than ±3dB from the initial value, nor have any significant damage after any of following testing.

#### **High Temperature Test**

High Temperature +85±2°C

**Duration** 96 hours

#### **Low Temperature Test**

**Low Temperature** -20±2°C

**Duration** 96 hours

### **Heat Shock Test**

High Temperature +85±2°C

Low Temperature -20±2°C

**Changeover Time** < 30 seconds

**Duration** 1 hour

Cycle 100

## **Humidity Test**

Temperature + 40±2°C

**Relative Humidity** 90%~95%

**Duration** 96 hours

# **Temperature Cycle Test**

Temperature -20°C +60°C

**Duration** 45 minutes 45 minutes

**Temperature gradient** 1~3°C/min

Cycle 25

# **Drop Test**

Mounted with dummy set mass 100 g

Height 1.5 m

Cycle 6 (1 each plain) onto the concrete board

#### **Load Test**

**Speaker mode:** White noise (EIA filter) for 96 hours @ 0.5W input power.



# SP DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

**Product Number: SP-1605-5** 



# Release | Revision: C/2018

## **CONTENTS**

This document contains the technical specifications for the dynamic speaker unit.

# Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

# Page 2

**Reliability Tests** 

# Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

## Page 4

Frequency Response Curve

### Page 5

Dimensions

#### Page 6

**Packing** 

# Measuring Method (Speaker Mode)

#### **Standard Test Condition**

Temperature 15 ~ 35°C

Relative humidity 45% ~ 85%

Atmospheric pressure 860mbar to 1060mbar

#### **Standard Test Fixture**

Input Power 0.1W


Zero Level -dB

Mode TSR

Potentiometer Range 50dB

Sweep Time 0.5sec

# **Standard Test Condition of Speaker (Fig. 1)**



soberton inc.



# SP DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

**Product Number: SP-1605-5** 



Release | Revision: C/2018

# **CONTENTS**

This document contains the technical specifications for the dynamic speaker unit.

# Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

# Page 2

**Reliability Tests** 

# Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

# Page 4

Frequency Response Curve


# Page 5

Dimensions

#### Page 6

Packing

# Frequency Response Curve (Fig. 2)





# SP DYNAMIC SPEAKER UNIT

**Acoustic Product Specification** 

**Product Number: SP-1605-5** 



Release | Revision: C/2018

# CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

# Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

# Page 2

**Reliability Tests** 

# Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

## Page 4

Frequency Response Curve

# Page 5


Dimensions


# Page 6

Packing

# **Dimensions**

Tolerance: ±0.5 (unit: mm)





No.	Part Name	Material	Quantity
1	UL1571 AWG32#	Wire Red/Black	2
2	PCB	FR-4	1
3	Frame	PBT	1
4	Magnet	Nd Fe B-N38-H	1
5	Plate	SPCC	1
6	Voice Coil	Copper	1
7	Membrane	PEN	1
8	Сар	SUS303	1
9	Gasket	Black Cloth	1
10	Screen	Black Cloth	1



# **SP DYNAMIC SPEAKER UNIT**

**Acoustic Product Specification** 

**Product Number: SP-1605-5** 



Release | Revision: C/2018

# **CONTENTS**

This document contains the technical specifications for the dynamic speaker unit.

# Page 1

Speaker Electroacoustic Characteristics

**General Specifications** 

# Page 2

Reliability Tests

# Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

# Page 4

Frequency Response Curve

# Page 5

**Dimensions** 

#### Page 6

**Packing** 

# **Packing**

## 100PCS

