

Tel: 1-800-722-8197 1-631-595-2217 Fax: 1-631-667-5484

EMAIL: sales@challelec.com WEB: www.challengeelectronics.com ISO 9001/14001:2015 Certified

INDICATORS • SPEAKERS • SOUND TRANSDUCERS • ENCLOSURES • MICROPHONES • BATTERY ACCESSORIES

CS13-00P20-03-1X

Rev. 1-2021 **RoHS3 & REACH IP67 Front Face Receiver Speakers**




Operating Characteristics

-		
ELEC	CTRICAL	
	Rated Power	0.01 W
	Short Term Max Power	0.02 W
	Impedance	$32 \Omega \pm 15 \%$ 1000 Hz; 0.001 W

ACOUSTIC: IEC-318 Artificial Ear

fo	200 Hz ± 20 % 0.001 W
Freq. Range	20 to 20000 Hz
Rated SPL	110 ± 3 dB 1000 Hz; 0.001 W;
Distortion	Max 5 % 50 and 5000 Hz; 0.001 W



Physical Characteristics


MAT	EF	AIS	LS

Housing	PPA	
Cone	Copper Edged PEEK	
Magnet	NdFeB	
Solder Pads	Stainless Steel	


TEMPERATURE RANGES

Operating	-25 to +50 °C
Storage	-25 to +60 °C

Weight 0.8 g



Unless otherwise specified,tolerance: ±0.2 (unit:mm)



All Measurements are mm unless noted otherwise.

Revision	Description	Ву	Date
0-2021	Original Specification	CT	2021-03-15
1-2021	Updated mechanical drawing. Updated form factor callout from Round Speaker to Receiver Speaker.	CT	2021-07-30

Warranty: For a period of one (1) year from date of shipping under normal operations conditions. This warranty does not apply to products damaged through misuse, abuse, improper installation, alteration, rework, or attempt to repair.