Technical Data Sheet



SP5T Terminated Ramses N 12.4GHz Normally open 28Vdc Positive common Pins Terminals

PAGE 1/2 ISSUE 06-02-18 SERIE : SPnT PART NUMBER : R574103510

RF CHARACTERISTICS

Number of ways : 5

Frequency range : 0 - 12.4 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4
VSWR max	1.20	1.35	1.50
Insertion loss max	0.20 dB	0.35 dB	0.50 dB
Isolation min	80 dB	70 dB	60 dB
Average power (*)	400 W	250 W	200 W

TERMINATION IMPEDANCE : 50 Ohms

TERM. AVG. POWER AT 25° C : 1 W per termination / 3 W total power

ELECTRICAL CHARACTERISTICS

Actuator : NORMALLY OPEN

Nominal current ** : 102 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / POSITIVE COMMON Terminals : solder pins (250°C max. / 30 sec.)

MECHANICAL CHARACTERISTICS

Connectors : N female per MIL-C 39012
Life : 2 million cycles per position

Switching Time*** : <15 ms

Construction : Splashproof

Weight : <460 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)








SP5T Terminated Ramses N 12.4GHz Normally open 28Vdc Positive common Pins Terminals


PAGE 2/2 ISSUE 06-02-18 SERIE : SPnT PART NUMBER : R574103510

DRAWING




Voltage	RF Continuity	
+C -1	$IN \leftrightarrow 1$	
+C -2	$IN \leftrightarrow 2$	
+C -3	$IN \leftrightarrow 3$	
+C -4	$IN \leftrightarrow 4$	
+C -5	IN ↔ 5	

TERMINALS




LABEL



General tolerances : ±0,5 mm [0,02 in]

SCHEMATIC DIAGRAM



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.