soberton inc.

DYNAMIC SPEAKER UNIT

Acoustic Product Specification

Product Number: SP-4005-3Y



Release | Revision: A/2018

CONTENTS

This document contains the technical specifications for the dynamic speaker.

Page 1 Electrical Specification

Reliability Test

Page 2 Temperature Condition

Test Setup

Typical Frequency Response Curve

Page 3 Dimensions

	Electrical Specification
ltem	Specification
Dimensions	Ø40.0 x H5.5mm
Rated Input Power	0.5W
Maximum Input Power	0.8 W
Sound Pressure Level	91±3dB (Input : 0.1m/0.1W) at 1.2, 1.5, 1.8, 2.0kHz in average (0dB SPL=20µPa)
Impedance	32Ω±20% (at 1 KHz, 1V)
Lower Resonance Frequency	480±20%Hz
Frequency Response	f0 ~ 20kHz (at -10dB)
Distortion	5% max (at 1KHz, 0.1m/0.5W)
Operation	It shall be normal. Input 4VRMS sine wave.
Polarity	When a positive DC current is applied to the terminal marked (+), the diaphragm moves forward.

Reliability Test						
Item	Method of Test Standard					
Load Test	Input Power: 0.5W white noise Duration: 96 hours					
Humidity Test	Temperature: 40°C Relative Humidity: 90~95% Duration: 96 hours					
High Temperature Test	Temperature: 80°C Duration: 96 hours					
Low Temperature Test	Temperature: -20°C Duration: 96 hours					
Thermal Shock Test	High Temperature: 80°C Low Temperature: -20°C Number of Cycles: 5 cycles Duration of Exposure: 2 hours at each temperature Duration of Recovery: 1 hour					
Vibration Test	Amplitude: 1.5 mm Frequency: 10 ~ 55 Hz Sweep Time: 1 minute Axes: 3 axes Duration: 2 hours on each axes					

	Duration: 2 hours on each axes					
Drop Test	Drop an unpacked unit onto a board 20mm thick 10 times from a height of 100cm.					

www.soberton.com



1

soberton inc.

DYNAMIC SPEAKER UNIT

Acoustic Product Specification

Product Number: SP-4005-3Y



Release | Revision: A/2018

CONTENTS

This document contains the technical specifications for the dynamic speaker.

Page 1 Electrical Specification

Reliability Test

Page 2 Temperature Condition


Test Setup

Typical Frequency Response Curve


Page 3 Dimensions

Temperature Condition					
Item	Specification				
Operation Temperature Range	-20°C ~ 60°C				
Storage Temperature Range	-25°C ~ 80°C				

Test Setup



Typical Frequency Response Curve



30	30	50	100	200	300	500	1k	2k	3k	5k	10k	20k Hz
Distance Sp	peaker - Mic.	: 10.0cm, Delay	r: 0.3ms								Test Signal: A	PN8192
	?.0V In <u>2</u>	?7.6Pa Out	22 dB KHz 9	IG <u>D</u> UT			NoName	<u>s</u> n			0000 2	018-11-12 14:55:48

www.soberton.com



soberton inc.

DYNAMIC SPEAKER UNIT

Acoustic Product Specification

Product Number: SP-4005-3Y



Release | Revision: A/2018

CONTENTS

This document contains the technical specifications for the dynamic speaker.

Page 1 Electrical Specification

Reliability Test

Page 2 Temperature Condition


Test Setup


Typical Frequency Response Curve


Page 3 Dimensions

Dimensions

Tolerance: ± 0.2mm.







www.soberton.com

