Acoustic Product Specification

Product Number: SP-2014L



Release | Revision: B/2018

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1 Speaker Electroacoustic Characteristics

General Specifications

Page 2 **Reliability Tests**

Page 3 Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

Dynamic Speaker Electroacoustic Characteristics

Sound Pressure Level

90±3dB SPL @0.8, 1.0, 1.18 and 1.5 KHz in average (0dB SPL=20µPa) Measuring Condition: 0.1W (Sine wave) 10cm measured with baffler shown in Fig.1.

Frequency Response Curve

As shown in Figure 2

Response Frequency

1050±20%Hz @ 1V. (Without Baffler)

Input Power (Nominal and Maximum)

Rated Noise Power 0.7W

Short Term Max Power: 1.0W must be normal at a white noise (1W, F0 ~ 20KHz) for one minute

Operation Test

Must be free audible noise (buzzes and rattles)

(3K ~ 5KHz frequency range, input level up to 2.36 Vrms)

Distortion

Less than 10% @1KHz, 0.1M, 0.1W frequency range, input level up to 1W

General Specifications

Operating Temperature Range

-20°C~+60°C

Storage Temperature Range

-25°C~+70°C

Standard Test Conditions

Temperature 17°C~25°C

Relative Humidity 45%~80%(RH)

AC Impedance

Page 4 Frequency Response Curve

Page 5 Dimensions

Page 6 Packing 8±15%Ω (@2KHz 1V) without baffler

Dimension

Ø20.0x14.0x4.0 WIRE (100mm)

IP Level

IP50

www.soberton.com



1

Acoustic Product Specification

Product Number: SP-2014L



Release | Revision: B/2018

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1 Speaker Electroacoustic Characteristics

General Specifications

Page 2 **Reliability Tests**

Page 3 Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

Reliability Tests

The sound pressure as specified will neither deviate more than ±3dB from the initial value, nor have any significant damage after any of following testing.

High Temperature Test

High Temperature +60±2°C

Duration 96 hours

Low Temperature Test

Low Temperature -20±2°C

Duration 96 hours

Heat Shock Test

High Temperature +60±2°C

Low Temperature -20±2°C

Changeover Time < 30 seconds

Duration 1 hour

Cycle 100

Humidity Test

Temperature + 40±2°C

Relative Humidity 90%~95%

Duration 96 hours

Temperature Cycle Test

Temperature -20°C +60°C

Duration 45 minutes 45 minutes

Temperature gradient 1~3°C/min

Cycle 25

Drop Test

Mounted with dummy set mass 100 g

Height 1.5 m

Cycle 6 (1 each plain) onto the concrete board

Page 4 **Frequency Response Curve**

Page 5 Dimensions

Page 6 Packing

Load Test

Speaker mode: White noise (EIA filter) for 96 hours @ 0.7W input power.

www.soberton.com



Acoustic Product Specification

Product Number: SP-2014L



Release | Revision: B/2018

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1

Speaker Electroacoustic Characteristics

General Specifications

Page 2 **Reliability Tests**

Page 3 Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

Measuring Method (Speaker Mode)

Standard Test Condition

Temperature 15 ~ 35°C

Relative humidity 45% ~ 85%

Atmospheric pressure 860mbar to 1060mbar

Standard Test Fixture

Input Power 0.1W


Zero Level -dB

Mode TSR

Potentiometer Range 50dB

Sweep Time 0.5sec

Standard Test Condition of Speaker (Fig. 1)



Page 4 Frequency Response Curve

Page 5 Dimensions

Page 6 Packing

www.soberton.com



Acoustic Product Specification

Product Number: SP-2014L



Release | Revision: B/2018

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1

Speaker Electroacoustic Characteristics


General Specifications

Page 2 **Reliability Tests**

Page 3 Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

Frequency Response Curve (Fig. 2)



Page 4 Frequency Response Curve

Page 5 Dimensions

Page 6 Packing

www.soberton.com



4

Acoustic Product Specification

Product Number: SP-2014L



Release | Revision: B/2018

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1

Speaker Electroacoustic Characteristics

General Specifications


Page 2 **Reliability Tests**


Page 3 Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

Dimensions

Tolerance: ±0.5 (unit: mm)





No.	Part Name	Material	Quantity
1	UL1571 AWG32#	Red/Black	2
2	РСВ	FR-4	1
3	Frame	PBT	1
4	Magnet	Nd Fe B	1

Page 4 Frequency Response Curve

Page 5 Dimensions

Page 6 Packing

	_		
5	Plate	SPCC	1
6	Voice Coil	Copper	1
7	Membrane	PEN	1
8	Сар	SUS303	1
9	Gasket	Black Net	1
10	Screen	Black Net	1

0

www.soberton.com



Acoustic Product Specification

Product Number: SP-2014L



Release | Revision: B/2018

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1

Speaker Electroacoustic Characteristics

General Specifications


Page 2 **Reliability Tests**


Page 3 Measuring Method (Speaker Mode)


Standard Test Condition of Speakers

Packing


100PCS











Page 4 Frequency Response Curve

Page 5 Dimensions

Page 6 Packing

www.soberton.com



6