
SPECIFICATIONS					
PARAMETERS	VALUES	UNITS			
RATED INPUT POWER	1	W			
MAX INPUT POWER	3	W			
IMPEDANCE	8 ± 15%	OHM			
OUTPUT SPL @ 1W/0.5M	80 ± 3	dBA			
(AT 0.8, 1.0, 1.2, 1.5 Hz)	00 ± 3	UDA			
DISTORTION (MAX.)	5%	-			
RESONANT FREQUENCY	750 ± 20%	Hz			
FREQUENCY RANGE	250 ~ 20,000	Hz			
HOUSING MATERIAL	ABS	-			
CONE MATERIAL	CLOTH	-			
MAGNET MATERIAL	Nd-Fe-B	-			
OPERATING TEMPERATURE	-30 ~ +60	°C			
WEIGHT	4.5	grams			

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.

©2003, Projects Unlimited Inc.

0		REVISION HISTORY		
	LTR	DESCRIPTION	DATE	APPROVED
	-	RELEASED FROM ENGINEERING	5/17/2006	
	Α	REVISED WIDTH DIMENSION	10/17/07	
	В	REVISED HEIGHT DIMENSION & RESONENT FREQUENCY	8/28/2008	C.W.
	С	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	10/7/2008	B.R.
	D	REVISED OPERATING TEMPERATURE	10/12/2011	M.L.
	Е	REVISED HOLE TO HOLE DIMENSION AND RESONANT FREQUENCY	2/11/2015	M.L.





## NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
- 3. THIS PART IS RoHS 2011/65/EU COMPLIANT.

TED:	UNLESS OTHERWISE SPECIFIED:
-	DIMENSIONS ARE IN MILLIMETERS.
NCES AND A3	TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.
)2708CO-R.idw	AS027080

	Designed by	Date	Checked by	Date	Approved by	Date	[	Drawn Date
	J.D.	5/17/2006	R.W.	5/17/2006	B.R.	5/17/20	006 1	0/7/2008
pul.			AS02708CO-R					
		a projects unlimited co	INC empany	Spe	aker		Edition _	Sheet 1 / 1