


### Heritage Series G12-65



Originally created in the late 70s using more modern materials and techniques for a higher power handling, the G12-65 is widely regarded as one of the best speakers ever produced for use in a 4x12 cabinet. With its fast attack and tightly controlled low-end, the G12-65 had become a firm favourite with hard rock players by the early 80s. The precisely tuned mid-range and crisp defined top-end contribute to an aggressive crunch sound that punches through the mix while the mid-range warmth and detail give weight and depth to single notes.

#### 8 Frequency Response



#### General Specifications

Nominal diameter	12", 305mm
Power rating	65Wrms
Nominal impedance	Available 8 or 15
Sensitivity	97dB
Chassis type	Pressed steel
Voice coil diameter	1.75", 44.5mm
Voice coil material	Round copper
Magnet type	Ceramic
Magnet weight	35oz, 0.99kg
Frequency range	80-5000Hz
Resonance frequency, Fs	85Hz
DC resistance, Re	Available 6.9 or 11.8

#### Mounting Information

Cut-out diameter	11.1", 283mm
Diameter	12.2", 309mm
Magnet structure diameter	5.7", 145mm
Mounting slot dimensions	0.31", 7.9mm Ø
Mounting slot PCD	11.7", 297mm
Number of mounting slots	4
Overall depth	5.0", 128mm
Unit weight	7.7lb, 3.5kg