Technical Data Sheet



DPDT Ramses SMA 3GHz Latching Indicators 12Vdc Positive common Pins Terminals

PAGE 1/2 ISSUE 26-01-17 SERIE : DPDT PART NUMBER : R577342012

RF CHARACTERISTICS

Frequency range : 0 - 3 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3
VSWR max	1.20
Insertion loss max	0.20 dB
Isolation min	80 dB
Average power (*)	240 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING
Nominal current ** : 320 mA

Actuator voltage (Vcc) : 12V (10.2 to 13V) / POSITIVE COMMON
Terminals : solder pins (250°C max. / 30 sec.)

Indicator rating : 1 W / 30 V / 100 mA

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 2.5 million cycles

Switching Time*** : <15 ms

Construction : Splashproof

Weight : <100 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)




Technical Data Sheet





DPDT Ramses SMA 3GHz Latching Indicators 12Vdc Positive common

Pins Terminals

PAGE 2/2 ISSUE 26-01-17 SERIE : DPDT PART NUMBER : R577342012








General tolerances: ±0,5 mm [0,02 in]

SCHEMATIC DIAGRAM



LABEL	
F1-2 +C 1 2 C RADIALL® R577342012 0 - 3 GHz Un: 12V Lot:	

Voltage	RF Continuity	Ind.
+C -1	$1 \leftrightarrow 3 / 2 \leftrightarrow 4$	C.1
+C -2	$1 \leftrightarrow 2 \ / \ 3 \leftrightarrow 4$	C.2