Technical Data Sheet



DPDT Ramses N 12.4GHz Latching 28Vdc Positive common D-sub connector

with bracket

PAGE 1/2 ISSUE 19.01.15 SERIE : DPDT PART NUMBER : R577133015

RF CHARACTERISTICS

Frequency range : 0 - 12.4 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 1	1 - 2	2 - 3	3 - 8	8 - 12.4
VSWR max	1.15	1.20	1.25	1.35	1.50
Insertion loss max	0.15 dB	0.20 dB	0.25 dB	0.35 dB	0.50 dB
Isolation min	85 dB	80 dB	75 dB	70 dB	60 dB
Average power (*)	700 W	500 W	400 W	250 W	200 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING
Nominal current ** : 125 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / POSITIVE COMMON

Terminals : 9 pins D-SUB male connector

MECHANICAL CHARACTERISTICS

Connectors : N female per MIL-C 39012

Life : 2.5 million cycles

Switching Time*** : <15 ms

Construction : Splashproof

Weight : < 215 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)








DPDT Ramses N 12.4GHz Latching 28Vdc Positive common D-sub connector


with bracket

PAGE 2/2 ISSUE 19.01.15 SERIE : DPDT PART NUMBER : R577133015

DRAWING




LABEL



General tolerances: ±0.5 mm

SCHEMATIC DIAGRAM



Voltage	RF Continuity
+C -1	$1 \leftrightarrow 3 / 2 \leftrightarrow 4$
+C -2	$1 \leftrightarrow 2 / 3 \leftrightarrow 4$