Technical Data Sheet



DPDT Ramses SMA 18GHz Latching 28Vdc Diodes Pins Terminals

PAGE 1/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577433032

RF CHARACTERISTICS

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18
VSWR max	1.20	1.30	1.40	1.50
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB
Isolation min	80 dB	70 dB	65 dB	60 dB
Average power (*)	240 W	150 W	120 W	100 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING
Nominal current ** : 125 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / NEGATIVE COMMON Terminals : solder pins (250°C max. / 30 sec.)

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 2.5 million cycles

Switching Time*** : < 15 ms

Construction : Splashproof

Weight : < 100 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)



Technical Data Sheet

PART NUMBER: **R577433032**



DPDT Ramses SMA 18GHz Latching 28Vdc Diodes Pins Terminals

PAGE **2/2** ISSUE **22-03-22** SERIE: DPDT **DRAWING** 0.909 23.10 4 x M3 depth 3.50 [0.138 min.] 3.50 min. 0.303 max.] 7.70 max. 1.555 max. 39.50 max. General tolerances: ±0,5 mm [0,02 in]




LABEL

RADIALL® R577433032 0 - 18 GHz

+1 +2 -C

Un : 28V Lot : _ _ _ _

SCHEMATIC DIAGRAM



Voltage	RF Continuity		
-C +1	$1 \leftrightarrow 3 / 2 \leftrightarrow 4$		
-C +2	$1 \leftrightarrow 2 / 3 \leftrightarrow 4$		