## **Technical Data Sheet**



SPDT Terminated Ramses SMA 18GHz Failsafe 28Vdc TTL Diodes External loads Pins terminals

ISSUE 09-03-21 SERIE : SPDT ZC PART NUMBER : R585413500

### **RF CHARACTERISTICS**

PAGE 1/2

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18
VSWR max	1.20	1.30	1.40	1.50
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB
Isolation min	80 dB	70 dB	60 dB	60 dB
Average power (*)	240 W	150 W	120 W	100 W

### **ELECTRICAL CHARACTERISTICS**

Actuator : FAILSAFE
Nominal current \*\* : 205 mA

Actuator voltage (Vcc) : 28V (24 to 30V)

Terminals : solder pins (250°C max. / 30 sec.)

TTL inputs (E) - High level : **2.2 to 5.5 V / 800μA at 5.5 V** 

- Low level : 0 to 0.8 V / 20µA at 0.8 V

## MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 10 million cycles

Switching Time\*\*\* : < 10 msConstruction : Splashproof
Weight : < 100 g

## **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(\* Average power at 25°C per RF Path)

(\*\* At 25° C ±10%)

(\*\*\* Nominal voltage; 25° C)



# **Technical Data Sheet**



SPDT Terminated Ramses SMA 18GHz Failsafe 28Vdc TTL Diodes External loads Pins terminals

