Technical Data Sheet



SPDT Terminated Ramses SMA 3GHz Failsafe 28Vdc Diodes Internal loads Pins terminals

SERIE: SPDT ZC PART NUMBER: R585313230

RF CHARACTERISTICS

PAGE 1/2

Frequency range : 0 - 3 GHz Impedance : 50 Ohms

ISSUE **09-03-21**

Frequency (GHz)	DC - 3
VSWR max	1.20
Insertion loss max	0.20 dB
Isolation min	80 dB
Average power (*)	240 W

ELECTRICAL CHARACTERISTICS

Actuator : FAILSAFE
Nominal current ** : 205 mA

Actuator voltage (Vcc) : 28V (24 to 30V)

Terminals : solder pins (250°C max. / 30 sec.)

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 2 million cycles
Switching Time*** : < 10 ms
Construction : Splashproof
Weight : < 100 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)



Technical Data Sheet



SPDT Terminated Ramses SMA 3GHz Failsafe 28Vdc Diodes Internal loads Pins terminals

PAGE **2/2** ISSUE **09-03-21** SERIE: SPDT ZC PART NUMBER: **R585313230 DRAWING** [2.189] 55.6 0.44 0.44 11.18 11.18 [0.138 min.] **LABEL** 3.5 min. 0 - 3 GHz Un: 28V **RADIALL®** R585313230 Lot:____ [0.122] [0.094]4 x Ø 3.1 NO С NC [0.059 max.] 1.5 max. [0.303 max.] 7.7 max. [0.441] 11.2 [1.321] 33.55 General tolerances: ±0,5 mm [0,02 in] **SCHEMATIC DIAGRAM** RF input 50Ω Termination Actuator ₹W0--9 RF Continuity Position De-energized →NC / NO↔500 NO 0 energized C↔NO / NC↔50Ω Power input terminals 50Ω Termination Position : de-energized