

HCBB62X2




金属化聚丙烯膜抗干扰电容器(X2类, 275Va.c./305Va.c./310Va.c./350Va.c.)




特点

- 用于电源跨线路抗干扰场合
- 金属化聚丙烯膜, 阻燃塑壳, 环氧树脂灌封
- 能承受过压冲击, 自愈性能优异
- 优异的阻燃、防潮性能
- 耐压高、绝缘电阻高

安全认证

	CQC	GB/T 6346.14	0.001 μ F-25 μ F;X2; \pm 10%(K), \pm 20%(M); 275/305/310/330/350Va.c.; 40/110/56B; 40/100/56B; 40/100/21B; 40/85/21B;40/85/56B 证书号: CQC21001289371
	ENEC-VDE	EN 60384-14 IEC 60384- 14	0.001 μ F-25 μ F,X2, \pm 10%(K), \pm 20%(M), 275/305/310/330/350Va.c.; 40/110/56B; 40/100/56B; 40/100/21B; 40/85/21B;40/85/56B 证书号: 125834
	UL/CUL	UL 60384-14 CSA E60384 - 1:14 CSA E60384 - 14:14	0.001 μ F-25 μ F,X2, \pm 10%(K), \pm 20%(M), 250/275/305/310/330/350Va.c.; 40/110/56B; 40/100/56B; 40/100/21B; 40/85/21B;40/85/56B 证书号: E311928,CCN:FOWX2/8

外形图



备注: 产品外形尺寸以mm为单位, 具体尺寸详见《产品尺寸表》。

技术要求

引用标准	GB/T 6346.14 (IEC 60384-14)		
气候类别/阻燃等级	40/110/56/B		
工作温度范围	-40°C ~+110°C		
额定电压	275Va.c./305Va.c./310Va.c./350Va.c.		
电容量范围	0.001μF~25.0μF		
电容量偏差	±10%(K),±20%(M) (20°C,1kHz)		
耐电压	引线之间	4.3U _R (5s)	
	极壳之间	2120Va.c. (1min)	
绝缘电阻	≥15 000MΩ, C _N ≤0.33μF ≥5 000s, C _N >0.33μF		(20°C,100Vd.c.,1min)
损耗角正切	0.001μF≤C _N ≤0.01μF	≤0.0020(1kHz,20°C)	≤0.0020(10kHz,20°C)
	0.01μF<C _N ≤0.47μF	≤0.0010(1kHz,20°C)	≤0.0020(10kHz,20°C)
	0.47μF<C _N ≤1.0μF	≤0.0020(1kHz,20°C)	≤0.0040(10kHz,20°C)
	1.0μF<C _N ≤10.0μF	≤0.0030(1kHz,20°C)	
	10.0μF<C _N ≤25.0μF	≤0.0040(1kHz,20°C)	

产品订货标记

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26
H	C	B	B	6	2	X	2	/									*	*	*	*	(x	x	x)
电容器代码									交流额定电压代码		标称容量代码		容量偏差代码	引线脚距 P代码	内部特征码	引线加工和包装代码		内部特征码							
									E2=250V P2=275V Q2=305V Q3=310V R2=350V		举例: 224=22×10 ⁴ pF =0.22μF		K=±10% M=±20%	3=7.5mm 4=10mm 6=15mm 9=22.5mm B=27.5mm F=37.5mm M=52.5mm	0 (普通品) M(内串结构)	见表1		需要区分特殊要求时使用							

表1: 引出端代码

第18位		第19位		第20位		第21位	
代码	说明	代码	说明	代码	说明	代码	说明
A	编带包装	3	F=7.5	0	表示直脚	1	产品在连续的两个载孔带之间 P=12.7mm,H0=18mm(Pitch=7.5)
		4	F=10.0			5	P=25.4mm,H0=18mm(Pitch=10.0/15.0)
		6	F=15.0				
C	直脚(散包)	00	标准的引线长度(18±1mm)		0	引线长度偏差±0.5mm或标准长度	
		35	引线长度3.5mm ⁽¹⁾				

备注: (1)若引线长度4.5mm, 则代码为C450, 以此类推。

产品尺寸

250Va.c./275Va.c./305Va.c./310Va.c.													
C _N (μF)	W (mm)	H (mm)	T (mm)	P (mm)	d (mm)	产品订货标记	C _N (μF)	W (mm)	H (mm)	T (mm)	P (mm)	d (mm)	产品订货标记
0.0010	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3102-30****	0.018	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3183-30****
0.0012	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3122-30****	0.022	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3223-30****
0.0015	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3152-30****	0.027	10.0	11.0	5.0	7.5	0.6	HCBB62X2/Q3273-30****
0.0018	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3182-30****	0.033	10.0	11.0	5.0	7.5	0.6	HCBB62X2/Q3273-30****
0.0022	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3222-30****	0.039	10.0	11.0	5.0	7.5	0.6	HCBB62X2/Q3393-30****
0.0027	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3272-30****	0.047	10.0	12.0	6.0	7.5	0.6	HCBB62X2/Q3473-30****
0.0033	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3332-30****	0.047	13.0	9.0	4.0	10.0	0.6	HCBB62X2/Q3472-40****
0.0039	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3392-30****	0.0056	13.0	9.0	4.0	10.0	0.6	HCBB62X2/Q3562-40****
0.0047	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3472-30****	0.0068	13.0	9.0	4.0	10.0	0.6	HCBB62X2/Q3682-40****
0.0056	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3562-30****	0.0082	13.0	9.0	4.0	10.0	0.6	HCBB62X2/Q3822-40****
0.0068	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3682-30****	0.01	13.0	9.0	4.0	10.0	0.6	HCBB62X2/Q3103-40****
0.0082	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3822-30****	0.012	13.0	9.0	4.0	10.0	0.6	HCBB62X2/Q3123-40****
0.01	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3103-30****	0.015	13.0	9.0	4.0	10.0	0.6	HCBB62X2/Q3153-40****
0.012	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3123-30****	0.018	13.0	9.0	4.0	10.0	0.6	HCBB62X2/Q3183-40****
0.015	10.0	9.0	4.0	7.5	0.6	HCBB62X2/Q3153-30****	0.022	13.0	9.0	4.0	10.0	0.6	HCBB62X2/Q3223-40****

备注:(1)“-”表示容量等级, K=±10%, M=±20%; “****”表示引线加工和包装代码(见表1);
(2)当额定交流电压为275Va.c.时, 第11~12位为P2。

产品尺寸

250Va.c./275Va.c./305Va.c./310Va.c.													
CN (μ F)	W (mm)	H (mm)	T (mm)	P (mm)	d (mm)	产品订货标记	CN (μ F)	W (mm)	H (mm)	T (mm)	P (mm)	d (mm)	产品订货标记
0.027	13.0	9.0	4.0	10.0	0.6	HCBB62X2/Q3273-40****	0.47	18.0	16.0	10.0	15.0	0.8	HCBB62X2/Q3474-60****
0.033	13.0	9.0	4.0	10.0	0.6	HCBB62X2/Q3333-40****	0.56	18.0	19.0	11.0	15.0	0.8	HCBB62X2/Q3564-60****
0.039	13.0	9.0	4.0	10.0	0.6	HCBB62X2/Q3393-40****	0.68	18.0	19.0	11.0	15.0	0.8	HCBB62X2/Q3684-60****
0.047	13.0	11.0	5.0	10.0	0.6	HCBB62X2/Q3473-40****	0.15	26.5	15.0	6.0	22.5	0.8	HCBB62X2/Q3154-90****
0.056	13.0	11.0	5.0	10.0	0.6	HCBB62X2/Q3563-40****	0.22	26.5	15.0	6.0	22.5	0.8	HCBB62X2/Q3224-90****
0.068	13.0	11.0	5.0	10.0	0.6	HCBB62X2/Q3683-40****	0.27	26.5	15.0	6.0	22.5	0.8	HCBB62X2/Q3274-90****
0.082	13.0	12.0	6.0	10.0	0.6	HCBB62X2/Q3823-40****	0.33	26.5	15.0	6.0	22.5	0.8	HCBB62X2/Q3334-90****
0.10	13.0	12.0	6.0	10.0	0.6	HCBB62X2/Q3104-40****	0.39	26.5	15.0	6.0	22.5	0.8	HCBB62X2/Q3394-90****
0.12	13.0	13.0	7.0	10.0	0.6	HCBB62X2/Q3124-40****	0.47	26.5	16.0	7.0	22.5	0.8	HCBB62X2/Q3474-90****
0.15	13.0	13.0	7.0	10.0	0.6	HCBB62X2/Q3154-40****	0.56	26.5	16.0	7.0	22.5	0.8	HCBB62X2/Q3564-90****
0.010	18.0	11.0	5.0	15.0	0.6	HCBB62X2/Q3103-60****	0.68	26.5	17.0	8.5	22.5	0.8	HCBB62X2/Q3684-90****
0.012	18.0	11.0	5.0	15.0	0.6	HCBB62X2/Q3123-60****	0.82	26.5	19.0	10.0	22.5	0.8	HCBB62X2/Q3824-90****
0.015	18.0	11.0	5.0	15.0	0.6	HCBB62X2/Q3153-60****	1.0	26.5	19.0	10.0	22.5	0.8	HCBB62X2/Q3105-90****
0.018	18.0	11.0	5.0	15.0	0.6	HCBB62X2/Q3183-60****	1.2	26.5	20.0	11.0	22.5	0.8	HCBB62X2/Q3125-90****
0.022	18.0	11.0	5.0	15.0	0.6	HCBB62X2/Q3223-60****	1.5	26.5	22.0	12.0	22.5	0.8	HCBB62X2/Q3155-90****
0.027	18.0	11.0	5.0	15.0	0.6	HCBB62X2/Q3273-60****	1.8	26.5	24.5	15.5	22.5	0.8	HCBB62X2/Q3185-90****
0.033	18.0	11.0	5.0	15.0	0.6	HCBB62X2/Q3333-60****	2.2	26.5	24.5	15.5	22.5	0.8	HCBB62X2/Q3225-90****
0.039	18.0	11.0	5.0	15.0	0.6	HCBB62X2/Q3393-60****	0.33	32.0	18.0	9.0	27.5	0.8	HCBB62X2/Q3334-B0****
0.047	18.0	11.0	5.0	15.0	0.6	HCBB62X2/Q3473-60****	0.39	32.0	18.0	9.0	27.5	0.8	HCBB62X2/Q3394-B0****
0.056	18.0	11.0	5.0	15.0	0.6	HCBB62X2/Q3563-60****	0.47	32.0	18.0	9.0	27.5	0.8	HCBB62X2/Q3474-B0****
0.068	18.0	11.0	5.0	15.0	0.6	HCBB62X2/Q3683-60****	0.56	32.0	18.0	9.0	27.5	0.8	HCBB62X2/Q3564-B0****
0.082	18.0	11.0	5.0	15.0	0.6	HCBB62X2/Q3823-60****	0.68	32.0	18.0	9.0	27.5	0.8	HCBB62X2/Q3684-B0****
0.10	18.0	11.0	5.0	15.0	0.6	HCBB62X2/Q3104-60****	0.82	32.0	18.0	9.0	27.5	0.8	HCBB62X2/Q3824-B0****
0.12	18.0	11.0	5.0	15.0	0.6	HCBB62X2/Q3124-60****	1.0	32.0	18.0	9.0	27.5	0.8	HCBB62X2/Q3105-B0****
0.15	18.0	12.0	6.0	15.0	0.8	HCBB62X2/Q3154-60****	1.2	32.0	20.0	11.0	27.5	0.8	HCBB62X2/Q3125-B0****
0.18	18.0	12.0	6.0	15.0	0.8	HCBB62X2/Q3184-60****	1.5	32.0	20.0	11.0	27.5	0.8	HCBB62X2/Q3155-B0****
0.22	18.0	13.5	7.5	15.0	0.8	HCBB62X2/Q3224-60****	1.8	32.0	22.0	13.0	27.5	0.8	HCBB62X2/Q3185-B0****
0.27	18.0	13.5	7.5	15.0	0.8	HCBB62X2/Q3274-60****	2.2	32.0	25.0	13.0	27.5	0.8	HCBB62X2/Q3225-B0****
0.33	18.0	14.5	8.5	15.0	0.8	HCBB62X2/Q3334-60****	2.7	32.0	24.5	15.0	27.5	0.8	HCBB62X2/Q3275-B0****
0.39	18.0	14.5	8.5	15.0	0.8	HCBB62X2/Q3394-60****	3.3	32.0	28.0	17.0	27.5	0.8	HCBB62X2/Q3335-B0****

备注:(1)“-”表示容量等级, K=±10%, M=±20%; “****”表示引线加工和包装代码(见表1);
(2)当额定交流电压为275Va.c.时, 第11~12位为P2。

产品尺寸

250Va.c./275Va.c./305Va.c./310Va.c.													
CN (μ F)	W (mm)	H (mm)	T (mm)	P (mm)	d (mm)	产品订货标记	CN (μ F)	W (mm)	H (mm)	T (mm)	P (mm)	d (mm)	产品订货标记
3.9	32.0	33.0	18.0	27.5	0.8	HCBB62X2/Q3395-B0****	5.6	42.0	33.5	18.5	37.5	1.0	HCBB62X2/Q3565-F0****
4.7	32.0	37.0	22.0	27.5	0.8	HCBB62X2/Q3475-B0****	6.8	42.0	33.5	18.5	37.5	1.0	HCBB62X2/Q3685-F0****
1.5	42.0	22.0	11.0	37.5	1.0	HCBB62X2/Q3155-F0****	8.2	42.0	37.0	22.0	37.5	1.0	HCBB62X2/Q3825-F0****
1.8	42.0	22.0	11.0	37.5	1.0	HCBB62X2/Q3185-F0****	10.0	42.0	41.0	26.0	37.5	1.0	HCBB62X2/Q3106-F0****
2.2	42.0	24.0	13.0	37.5	1.0	HCBB62X2/Q3225-F0****	12.0	42.0	43.0	28.0	37.5	1.0	HCBB62X2/Q3126-F0****
2.7	42.0	24.0	13.0	37.5	1.0	HCBB62X2/Q3275-F0****	15.0	42.0	45.0	30.0	37.5	1.0	HCBB62X2/Q3156-F0****
3.3	42.0	28.0	14.0	37.5	1.0	HCBB62X2/Q3335-F0****	20.0	57.5	45.0	30.0	52.5	1.2	HCBB62X2/Q3206-M0****
3.9	42.0	30.0	16.0	37.5	1.0	HCBB62X2/Q3395-F0****	25.0	57.5	50.0	35.0	52.5	1.2	HCBB62X2/Q3256-M0****
4.7	42.0	30.0	16.0	37.5	1.0	HCBB62X2/Q3475-F0****							
350Va.c.													
CN (μ F)	W (mm)	H (mm)	T (mm)	P (mm)	d (mm)	产品订货标记	CN (μ F)	W (mm)	H (mm)	T (mm)	P (mm)	d (mm)	产品订货标记
0.010	13.0	9.0	4.0	10.0	0.6	HCBB62X2/R2103-4M****	0.047	18.0	11.0	5.0	15.0	0.6	HCBB62X2/R2473-6M****
0.012	13.0	9.0	4.0	10.0	0.6	HCBB62X2/R2123-4M****	0.056	18.0	11.0	5.0	15.0	0.6	HCBB62X2/R2563-6M****
0.015	13.0	9.0	4.0	10.0	0.6	HCBB62X2/R2153-4M****	0.068	18.0	12.0	6.0	15.0	0.6	HCBB62X2/R2683-6M****
0.018	13.0	9.0	4.0	10.0	0.6	HCBB62X2/R2183-4M****	0.082	18.0	12.0	6.0	15.0	0.6	HCBB62X2/R2823-6M****
0.022	13.0	9.0	4.0	10.0	0.6	HCBB62X2/R2223-4M****	0.10	18.0	12.0	6.0	15.0	0.6	HCBB62X2/R2104-6M****
0.027	13.0	11.0	5.0	10.0	0.6	HCBB62X2/R2273-4M****	0.12	18.0	13.5	7.5	15.0	0.6	HCBB62X2/R2124-6M****
0.033	13.0	11.0	5.0	10.0	0.6	HCBB62X2/R2333-4M****	0.15	18.0	13.5	7.5	15.0	0.6	HCBB62X2/R2154-6M****
0.039	13.0	11.0	5.0	10.0	0.6	HCBB62X2/R2393-4M****	0.18	18.0	14.5	8.5	15.0	0.8	HCBB62X2/R2184-6M****
0.047	13.0	12.0	6.0	10.0	0.6	HCBB62X2/R2473-4M****	0.22	18.0	14.5	8.5	15.0	0.8	HCBB62X2/R2224-6M****
0.056	13.0	12.0	6.0	10.0	0.6	HCBB62X2/R2563-4M****	0.27	18.0	16.0	10.0	15.0	0.8	HCBB62X2/R2274-6M****
0.010	18.0	11.0	5.0	15.0	0.6	HCBB62X2/R2103-6M****	0.33	18.0	19.0	11.0	15.0	0.8	HCBB62X2/R2334-6M****
0.012	18.0	11.0	5.0	15.0	0.6	HCBB62X2/R2123-6M****	0.10	26.5	15.0	6.0	22.5	0.8	HCBB62X2/R2104-9M****
0.015	18.0	11.0	5.0	15.0	0.6	HCBB62X2/R2153-6M****	0.12	26.5	15.0	6.0	22.5	0.8	HCBB62X2/R2124-9M****
0.018	18.0	11.0	5.0	15.0	0.6	HCBB62X2/R2183-6M****	0.15	26.5	15.0	6.0	22.5	0.8	HCBB62X2/R2154-9M****
0.022	18.0	11.0	5.0	15.0	0.6	HCBB62X2/R2223-6M****	0.18	26.5	15.0	6.0	22.5	0.8	HCBB62X2/R2184-9M****
0.027	18.0	11.0	5.0	15.0	0.6	HCBB62X2/R2273-6M****	0.22	26.5	15.0	6.0	22.5	0.8	HCBB62X2/R2224-9M****
0.033	18.0	11.0	5.0	15.0	0.6	HCBB62X2/R2333-6M****	0.27	26.5	15.0	6.0	22.5	0.8	HCBB62X2/R2274-9M****
0.039	18.0	11.0	5.0	15.0	0.6	HCBB62X2/R2393-6M****	0.33	26.5	16.0	7.0	22.5	0.8	HCBB62X2/R2334-9M****

备注:(1)“-”表示容量等级, K=±10%, M=±20%; “****”表示引线加工和包装代码(见表1);

(2)当额定交流电压为275Va.c.时,第11~12位为P2。

产品尺寸

350V.a.c.													
CN (μ F)	W (mm)	H (mm)	T (mm)	P (mm)	d (mm)	产品订货标记	CN (μ F)	W (mm)	H (mm)	T (mm)	P (mm)	d (mm)	产品订货标记
0.39	26.5	17.0	8.5	22.5	0.8	HCBB62X2/R2394-9M****	4.7	32.0	37.0	22.0	27.5	0.8	HCBB62X2/R2475-BM****
0.47	26.5	17.0	8.5	22.5	0.8	HCBB62X2/R2474-9M****	0.33	42.0	22.0	11.0	37.5	1.0	HCBB62X2/R2334-FM****
0.56	26.5	19.0	10.0	22.5	0.8	HCBB62X2/R2564-9M****	0.39	42.0	22.0	11.0	37.5	1.0	HCBB62X2/R2394-FM****
0.68	26.5	19.0	10.0	22.5	0.8	HCBB62X2/R2684-9M****	0.47	42.0	22.0	11.0	37.5	1.0	HCBB62X2/R2474-FM****
0.82	26.5	20.0	11.0	22.5	0.8	HCBB62X2/R2824-9M****	0.56	42.0	22.0	11.0	37.5	1.0	HCBB62X2/R2564-FM****
1.0	26.5	22.0	12.0	22.5	0.8	HCBB62X2/R2105-9M****	0.68	42.0	22.0	11.0	37.5	1.0	HCBB62X2/R2684-FM****
1.2	26.5	23.0	13.5	22.5	0.8	HCBB62X2/R2125-9M****	0.82	42.0	22.0	11.0	37.5	1.0	HCBB62X2/R2824-FM****
1.5	26.5	24.5	15.5	22.5	0.8	HCBB62X2/R2155-9M****	1.0	42.0	22.0	11.0	37.5	1.0	HCBB62X2/R2105-FM****
0.22	32.0	18.0	9.0	27.5	0.8	HCBB62X2/R2224-BM****	1.2	42.0	22.0	11.0	37.5	1.0	HCBB62X2/R2125-FM****
0.27	32.0	18.0	9.0	27.5	0.8	HCBB62X2/R2274-BM****	1.5	42.0	24.0	13.0	37.5	1.0	HCBB62X2/R2155-FM****
0.33	32.0	18.0	9.0	27.5	0.8	HCBB62X2/R2334-BM****	1.8	42.0	24.0	13.0	37.5	1.0	HCBB62X2/R2185-FM****
0.39	32.0	18.0	9.0	27.5	0.8	HCBB62X2/R2394-BM****	2.2	42.0	26.0	15.0	37.5	1.0	HCBB62X2/R2225-FM****
0.47	32.0	18.0	9.0	27.5	0.8	HCBB62X2/R2474-BM****	2.7	42.0	28.0	14.0	37.5	1.0	HCBB62X2/R2275-FM****
0.56	32.0	18.0	9.0	27.5	0.8	HCBB62X2/R2564-BM****	3.3	42.0	30.0	16.0	37.5	1.0	HCBB62X2/R2335-FM****
0.68	32.0	18.0	9.0	27.5	0.8	HCBB62X2/R2684-BM****	3.9	42.0	32.0	17.0	37.5	1.0	HCBB62X2/R2395-FM****
0.82	32.0	20.0	11.0	27.5	0.8	HCBB62X2/R2824-BM****	4.7	42.0	34.0	20.0	37.5	1.0	HCBB62X2/R2475-FM****
1.0	32.0	20.0	11.0	27.5	0.8	HCBB62X2/R2105-BM****	5.6	42.0	37.0	22.0	37.5	1.0	HCBB62X2/R2565-FM****
1.2	32.0	22.0	13.0	27.5	0.8	HCBB62X2/R2125-BM****	6.8M	42.0	37.0	22.0	37.5	1.0	HCBB62X2/R2685MFM****
1.5	32.0	25.0	13.0	27.5	0.8	HCBB62X2/R2155-BM****	6.8K	42.0	37.0	26.0	37.5	1.0	HCBB62X2/R2685KFM****
1.8	32.0	24.5	15.0	27.5	0.8	HCBB62X2/R2185-BM****	8.2	42.0	41.0	26.0	37.5	1.0	HCBB62X2/R2825-FM****
2.2	32.0	30.0	16.0	27.5	0.8	HCBB62X2/R2225-BM****	10.0	42.0	45.0	30.0	37.5	1.0	HCBB62X2/R2106-FM****
2.7	32.0	33.0	18.0	27.5	0.8	HCBB62X2/R2275-BM****	15.0	57.5	45.0	30.0	52.5	1.2	HCBB62X2/R2156-MM****
3.3	32.0	33.0	18.0	27.5	0.8	HCBB62X2/R2335-BM****	18.0	57.5	45.0	35.0	52.5	1.2	HCBB62X2/R2186-MM****
3.9	32.0	37.0	22.0	27.5	0.8	HCBB62X2/R2395-BM****	20.0	57.5	50.0	35.0	52.5	1.2	HCBB62X2/R2206-MM****

备注:(1)“-”表示容量等级, K=±10%, M=±20% ; “****”表示引线加工和包装代码(见表1)。