Technical Data Sheet



DPDT Ramses N 3GHz Latching 28Vdc Diodes D-sub connector with bracket

PAGE 1/2 ISSUE 26-01-17 SERIE : DPDT PART NUMBER : R577033035

RF CHARACTERISTICS

Frequency range : 0 - 3 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 1	1 - 2	2 - 3
VSWR max	1.15	1.20	1.25
Insertion loss max	0.15 dB	0.20 dB	0.25 dB
Isolation min	85 dB	80 dB	75 dB
Average power (*)	700 W	500 W	400 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING
Nominal current ** : 125 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / NEGATIVE COMMON

Terminals : 9 pins D-SUB male connector

MECHANICAL CHARACTERISTICS

Connectors : N female per MIL-C 39012

Life : 2.5 million cycles

Switching Time*** : <15 ms

Construction : Splashproof

Weight : <215 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.







DPDT Ramses N 3GHz Latching 28Vdc Diodes D-sub connector with bracket

PAGE 2/2 ISSUE 26-01-17 SERIE : DPDT PART NUMBER : R577033035


DRAWING







LABEL




RADIALL® R577033035 0 - 3 GHz Un : 28V Lot : _ _ _

☐ 44.40 ☐ General tolerances : ±0,5 mm [0,02 in]

[1.748]

SCHEMATIC DIAGRAM



Voltage	RF Continuity	
-C +1	$1 \leftrightarrow 3 / 2 \leftrightarrow 4$	
-C +2	$1 \leftrightarrow 2 / 3 \leftrightarrow 4$	