

Technical Data Sheet

DPDT Ramses SMA 26.5GHz Latching 28Vdc Pins Terminals


	Frequency range Impedance		: 0 - 26.5 GHz : 50 Ohms				
	Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18	18 - 26.5	
	VSWR max	1.20	1.30	1.40	1.50	1.70	
	Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB	0.70 dB	
	Isolation min	80 dB	70 dB	65 dB	60 dB	50 dB	
	Average power (*)	240 W	150 W	120 W	100 W	40 W	
	Actuator Nominal current ** Actuator voltage (Vcc Terminals)	:	LATCHING 125 mA 28V (24 to 3 solder pins		IVE COMMON / 30 sec.)	
MEC	HANICAL CHARACTE Connectors Life Switching Time*** Construction Weight	RISTICS	:	SMA female 2.5 million o < 15 ms Splashproo < 100 g	cycles	9012	
ENV	IRONMENTAL CHARA	CTERISTICS					
	Operating temperature	e range	:	-40°C to +8	5°C		
	Storage temperature			-55°C to +8		ROHS	
	Average power at 25°	C per RF Path)					·)
(*	At 25° C ±10%)	,				0	~
(* (**		C)				MPLIA	
(* (** (***	Nominal voltage ; 25°						

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.



Technical Data Sheet

DPDT Ramses SMA 26.5GHz Latching 28Vdc Pins Terminals



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.