Technical Data Sheet



SP8T Ramses SMA 26GHz Normaly open 28Vdc Pins Terminals

PAGE 1/2 ISSUE 05.06.15 SERIE : SPNT PART NUMBER : R573F03800

RF CHARACTERISTICS

Number of ways : 8

Frequency range : 0 - 26.5 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 16	16 - 18	18 - 22	22 - 26.5
VSWR max	1.20	1.30	1.40	1.50	1.60	1.70	2.00
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.55 dB	0.60 dB	0.70 dB	1.10 dB
Isolation min	80 dB	70 dB	60 dB	60 dB	60 dB	60 dB	55 dB
Average power (*)	240 W	150 W	120 W	110 W	100 W	90 W	40 W

ELECTRICAL CHARACTERISTICS

Actuator : NORMALLY OPEN

Nominal current ** : 102 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / NEGATIVE COMMON Terminals : solder pins (250°C max. / 30 sec.)

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012 Life : 2.000.000 cycles per position

Switching Time*** : <15 ms

Construction : Splashproof

Weight : < 280 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)




Technical Data Sheet




SP8T Ramses SMA 26GHz Normaly open 28Vdc Pins Terminals


PAGE 2/2 ISSUE 05.06.15 SERIE : SPnT PART NUMBER : R573F03800

DRAWING




Voltage	RF Continuity		
-C +1	$IN \leftrightarrow 1$		
-C +2	$IN \leftrightarrow 2$		
-C +3	$IN \leftrightarrow 3$		
-C +4	$IN \leftrightarrow 4$		
-C +5	$IN \leftrightarrow 5$		
-C +6	IN ↔ 6		
-C +7	$IN \leftrightarrow 7$		
-C +8	IN ↔ 8		





General tolerances: ±0.5 mm

SCHEMATIC DIAGRAM



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.