Technical Data Sheet



SP12T Terminated Ramses SMA 18GHz Latching Self-cut-off Auto-reset 28Vdc BCD TTL Diodes D-sub connector

PAGE 1/2 ISSUE 25-11-22 SERIE : SPnT PART NUMBER : R574F83285

RF CHARACTERISTICS

Number of ways : 12

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 15	15 - 18
VSWR max	1,20	1,40	1,60	1,70	1,80
Insertion loss max	0.20 dB	0.40 dB	0.60 dB	0.70 dB	0.80 dB
Isolation min	80 dB	70 dB	60 dB	60 dB	50 dB
Average power (*)	240 W	150 W	120 W	110 W	100 W

TERMINATION IMPEDANCE : 50 Ohms

TERM. AVG. POWER AT 25° C : 1 W per termination / 3 W total power

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING
Nominal current ** : 500 mA

Actuator voltage (Vcc) : 28V (24 to 30V)

Terminals : 44 pins D-SUB male connector

Self cut-off time : 40 ms < CT < 120 ms

BCD inputs (E) - High level : 3.5 to 5.5 V / 800 μ A at 5.5 V

- Low level : 0 to 1.5 V / 20µA at 0.8 V

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012 Life : 2 million cycles per position

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)


(*** Nominal voltage; 25° C)







SP12T Terminated Ramses SMA 18GHz Latching Self-cut-off Auto-reset 28Vdc BCD TTL Diodes D-sub connector



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.

RF inputs