



SPDT Terminated Ramses SMA 18GHz Failsafe Indicators 12Vdc Diodes Internal loads Pins terminals

PAGE 1/2 ISSUE 09-03-21 SERIE : SPDT ZC PART NUMBER : R585422230

### RF CHARACTERISTICS

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18
VSWR max	1.20	1.30	1.40	1.50
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB
Isolation min	80 dB	70 dB	60 dB	60 dB
Average power (*)	240 W	150 W	120 W	100 W

#### **ELECTRICAL CHARACTERISTICS**

Actuator : FAILSAFE
Nominal current \*\* : 500 mA

Actuator voltage (Vcc) : 12V (10.2 to 13V)

Terminals : solder pins (250°C max. / 30 sec.)

Indicator rating : 1 W / 30 V / 100 mA

#### MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 2 million cycles

Switching Time\*\*\* : < 10 ms

Construction : Splashproof

Weight : < 100 g

## ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(\* Average power at 25°C per RF Path)

(\*\* At 25° C ±10%)

(\*\*\* Nominal voltage; 25° C)



# **Technical Data Sheet**



SPDT Terminated Ramses SMA 18GHz Failsafe Indicators 12Vdc Diodes Internal loads Pins terminals

PAGE **2/2** ISSUE **09-03-21** SERIE: SPDT ZC PART NUMBER: **R585422230 DRAWING** 2.189 55.6 0.44 0.44 11.18 11.18 [0.138 min.] LABEL 3.5 min. 0 - 18 GHz 2N0 1NC C Un: 12V **RADIALL®** R585422230 Lot:\_\_\_\_ [0.122][0.094]NO С NC 4 x ¯ Ø 3.1 [0.059 max.] 1.5 max. 0.303 max. [0.441] 11.2 [1.321] 33.55 General tolerances: ±0,5 mm [0,02 in] **SCHEMATIC DIAGRAM** Indicator terminals RF input \_O 1NC \_o 2N0 50Ω Termination -O C Actuator \$-WV-RF Continuity Position Indicator De-energized C↔NC / NO↔50Ω C.1NC energized C↔NO / NC↔50Ω C.2NO NO 0-NC o-d Power input terminals \$-W0-0  $50\Omega$  Termination Position : de-energized