Technical Data Sheet



SP3T Ramses SMA 18GHz Latching 28Vdc TTL Diodes D-sub connector

PAGE 1/2 ISSUE 22-03-22 SERIE : SPnT PART NUMBER : R573423325

RF CHARACTERISTICS

Number of ways : 3

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18
VSWR max	1.20	1.30	1.40	1.50
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB
Isolation min	80 dB	70 dB	60 dB	60 dB
Average power (*)	240 W	150 W	120 W	100 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING

Nominal current ** : 125 mA / RESET : 375 mA ****

Actuator voltage (Vcc) : 28V (24 to 30V)

Terminals : 25 pins D-SUB male connector

TTL inputs (E) - High level : 2.2 to 5.5 V / $800\mu A$ at 5.5 V

- Low level : 0 to 0.8 V / 20µA at 0.8 V

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012 Life : 5 million cycles per position

Switching Time*** : <15 ms

Construction : Splashproof

Weight : < 220 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)

(**** Reset : supply voltage time 1sec. max. / duty cycle 10%)




Technical Data Sheet




SP3T Ramses SMA 18GHz Latching 28Vdc TTL Diodes D-sub connector

PAGE 2/2 ISSUE 22-03-22 SERIE : SPnT PART NUMBER : R573423325


DRAWING



TTL input	RF Continuity	
RESET = 1	All ports open	
E1 = 1	$IN \leftrightarrow 1$	
E2 = 1	$IN \leftrightarrow 2$	
E3 = 1	$IN \leftrightarrow 3$	




LABEL





•

SCHEMATIC DIAGRAM



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.