## TS63421K – 1.9Ω On Resistance GaN Broadband RF Switch SP4T

### 1.0 Features

- Ultra low 1.9Ω on resistance
- 0.35pF C<sub>off</sub>
- RF peak voltage handling of 100V
- Each state can be controlled independently
- 16 possible independent state configuration
- No external DC blocking capacitors on RF lines
- Versatile 2.6~5.5V power supply
- 1.2~5.0V digital control

## 2.0 Applications

- Filter and antenna tuning
- Dynamic matching
- Private mobile radio handsets
- Public safety handsets
- Cellular infrastructure
- Satellite terminals





Figure 1 Device Image (16 Pin 3x3x0.8mm QFN Package)



RoHS/REACH/Halogen Free Compliance

## 3.0 Description

The TS63421K is a reflective open Single Pole Four Throw (SP4T) switch designed for antenna or filter tuning applications where high RF peak voltage handling is desired. TS63421K is suitable for frequency range from 1MHz to 1GHz. The TS63421K has a very low  $1.9\Omega$  on resistance and off capacitance of 0.35 pF. This switch can select up to 16 independent states. The internal charge pump has also been disabled to eliminate the charge pump spurs. A -18V supply is needed on the Vcp pin.

The TS63421K is packaged in a compact Quad Flat No lead (QFN) 3x3mm 16 leads plastic package.




Figure 2 Function Block Diagram (Top View)

## 4.0 Ordering Information

**Table 1 Ordering Information** 

Base Part Number	Package Type	Form	Qty	Reel Diameter	Reel Width	Orderable Part Number
TS63421K	16 Pin 3×3×0.8mm QFN	Tape and Reel	3000	13" (330mm)	18mm	TS63421KMTRPBF
Evaluation Board						TS63421K-EVB

## 5.0 Pin Description

**Table 2 Pin Definition** 

Pin Number	Pin Name	Description
1	V1	Switch control input 1
2	V2	Switch control input 2
3	V3	Switch control input 3
4	V4	Switch control input 4
5,6,8,13,14	NC	No internal connection, can be grounded
7	ANT	Antenna port
9	RF4	RF port 4
10	RF3	RF port 3
11	RF2	RF port 2
12	RF1	RF port 1
15	VCP	Negative Voltage supply, -18V. Add 1nF to Gnd on this pin
16	VDD	DC power supply

**Note:** The backside ground (thermal) pad of the package must be grounded directly to the ground plane of PCB with multiple vias to ensure proper operation and thermal management.

## 6.0 Absolute Maximum Ratings

Table 3 Absolute Maximum Ratings @T<sub>A</sub>=+25°C Unless Otherwise Specified

Parameter	Symbol	Value	Unit				
Electrical Ratings							
Power Supply Voltage	VDD	2.6 to 5.5	V				
Charge Pump Voltage	VCP	-15 to -19	V				
Storage Temperature Range	T <sub>st</sub>	-55 to +125	°C				
Operating Temperature Range	T <sub>op</sub>	-40 to +85	°C				
Maximum Junction Temperature	TJ	+140	°C				
RF Input Power CW, 800MHz	RFx	41	dBm				
Thermal Rati	ngs						
Thermal Resistance (junction-to-case) – Bottom side	R <sub>θ</sub> JС	20	°C/W				
Thermal Resistance (junction-to-top)	R <sub>θ</sub> ЈТ	≤ 39	°C/W				
Soldering Temperature	T <sub>SOLD</sub>	260	°C				
ESD Rating	js						
Human Body Model (HBM)	Level 1B	500 to <1000	V				
Charged Device Model (CDM)	Level C3	≥1000	V				
Moisture Rating							
Moisture Sensitivity Level	MSL	1	-				

### Attention:

Maximum ratings are absolute ratings. Exposure to absolute maximum rating conditions for extended periods may affect device reliability. Exceeding one or a combination of the absolute maximum ratings may cause permanent and irreversible damage to the device and/or to surrounding circuit.

## 7.0 Electrical Specifications

**Table 4 Electrical Specifications**  $@T_A=+25^{\circ}C$  Unless Otherwise Specified; VDD=+2.7V; VCP = -18V,  $50\Omega$  Source/Load.

Parameter	Condition	Minimum	Typical	Maximum	Unit
Operating Frequency		1		1000	MHz
ON Resistance	On state, DC measurement		1.9		Ω
OFF Capacitance	Total capacitance of each OFF path		0.35		pF
RF Peak Voltage	Measured at 10MHz		100		V
Insertion Loss, RFx	100MHz		0.25		dB
	500MHz		0.40		
	1.0GHz		0.60		
Isolation ANT-RFx	100MHz		37		dB
	500MHz		25		
	1.0GHz		20		
Return Loss ANT-	100MHz		30		dB
RFx	500MHz		18		
	1.0GHz		16		
H2	800MHz, Pin=35dBm		80		dBc
H3	800MHz, Pin=35dBm		85		dBc
IIP3	800MHz		71		dBm
DO 4 dD[1]	1~10MHz		40		dBm
P0.1dB <sup>[1]</sup>	10~1000MHz		42		dBm
Switching Time	50% ctrl to 10/90% of the RF value is settled. C1=1nF to Gnd on VCP		2.0		μS
Start-up Time	50% ctrl to 10/90% of the RF value is settled. C1=1nF to Gnd on VCP		TBD		μS
Control Voltage	Power supply, VDD	2.6	2.7	5.5	V
	Charge Pump Supply, VCP	-19	-18	-15	V
	All control pins high, Vih	1.0	2.7	5.25	V
	All control pins low, Vil	-0.3		0.5	V
Control Current	All control pins low, Iii		0		μΑ
	All control pins high, Iih			7.5	μA
Current Consumption, IDD	Active mode		50	80	μΑ

### Note:

- [1] P0.1dB is a figure of merit.
- [2] No external DC blocking capacitors required on RF pins unless DC voltage is applied on a RF pin.
- [3] Start-up time is the time from VDD ON to RF signal settled on a throw or transition time from low power mode to active mode.

### 8.0 Switch Truth Table


**Table 5 Switch Truth Table** 


V1	V2	V3	V4	Active RF Path
0	0	0	0	All OFF state
0	0	0	1	RF4
0	0	1	0	RF3
0	0	1	1	RF3, RF4
0	1	0	0	RF2
0	1	0	1	RF2, RF4
0	1	1	0	RF2, RF3
0	1	1	1	RF2, RF3, RF4
1	0	0	0	RF1
1	0	0	1	RF1, RF4
1	0	1	0	RF1, RF3
1	0	1	1	RF1, RF3, RF4
1	1	0	0	RF1, RF2
1	1	0	1	RF1, RF2, RF4
1	1	1	0	RF1, RF2, RF3
1	1	1	1	All ON state

#### Attention:

- [1] VDD should be applied first before V1, V2, V3 and V4, otherwise may cause damage to the device.
- [2] There are internal pull-downs to ground on all control pins, the state at start-up without any control voltage applied will be All OFF.

### 9.0 Evaluation Board









Figure 4 Evaluation Board Image


**Table 6 Recommended Values** 

Component	Value	Unit	
Ср	0.25	pF	
Coff	0.35	pF	
Rswx	1.9 if ON	Ω	
RSWX	500K if OFF	Ω	
Ls	0.4	nH	

Note: Ron/Off is measured at DC. This model will not accurately predict losses in a tunable filter or antenna design

# **10.0 Typical Characteristics**





**Figure 5 Insertion Loss** 

Figure 6 RF2 - 4 Isolation






Figure 7 Return Loss

# 11.0 Device Package Information








Figure 8 Device Package Drawing

(All dimensions are in mm)

**Table 7 Device Package Dimensions** 

Dimension (mm)	Value (mm)	Tolerance (mm)	Dimension (mm)	Value (mm)	Tolerance (mm)
Α	0.80	±0.05	Е	3.00 BSC	±0.05
A1	0.203	±0.02	E1	1.70	±0.05
b	0.25	+0.05/-0.07	F	0.625	±0.05
D	3.00 BSC	±0.05	G	0.625	±0.05
D1	1.70	±0.05	L	0.25	±0.05
е	0.50 BSC	±0.05	K	0.40	±0.05

**Note:** Lead finish: Pure Sn without underlayer; Thickness: 7.5μm ~ 20μm (Typical 10μm ~ 12μm)

### Attention:

Please refer to application notes *TN-001* and *TN-002* at http://www.tagoretech.com for PCB and soldering related guidelines.

## 12.0 PCB Land Design

### **Guidelines:**

- [1] 4 layer PCB is recommended.
- [2] Via diameter is recommended to be 0.2mm to prevent solder wicking inside the vias.
- [3] Thermal vias shall only be placed on the center pad.
- [4] The maximum via number for the center pad is  $3(X)\times3(Y)=9$ .




Figure 9 PCB Land Pattern (Dimensions are in mm)

0.07Max
All Around

Metal Under
Solder Mask Opening

O.07Max
All Around

Metal Under
Solder Mask Opening

Non-Solder Mask Defined (Preferred)

Solder Mask Defined

## Figure 10 Solder Mask Pattern

(Dimensions are in mm)




Figure 11 Thermal Via Pattern

(Recommended Values: S≥0.15mm; Y≥0.20mm; d=0.2mm; Plating Thickness t=25µm or 50µm)

## 13.0 PCB Stencil Design

### **Guidelines:**

- [1] Laser-cut, stainless steel stencil is recommended with electro-polished trapezoidal walls to improve the paste release.
- [2] Stencil thickness is recommended to be 125µm.




Figure 12 Stencil Openings

(Dimensions are in mm)





Figure 13 Stencil Openings Shall not Cover Via Areas If Possible (Dimensions are in mm)

# 14.0 Tape and Reel Information



**Figure 14 Tape and Reel Drawing** 

**Table 8 Tape and Reel Dimensions** 

Dimension (mm)	Value (mm)	Tolerance (mm)	Dimension (mm)	Value (mm)	Tolerance (mm)
A0	3.35	±0.10	K0	1.10	±0.10
В0	3.35	±0.10	P0	4.00	±0.10
D0	1.50	+0.10/-0.00	P1	8.00	±0.10
D1	1.50	+0.10/-0.00	P2	2.00	±0.05
E	1.75	±0.10	Т	0.30	±0.05
F	5.50	±0.05	W	12.00	±0.30



### Edition Revision 1.1 - 2020-04-24

## **Published by**

Tagore Technology Inc. 5 East College Drive, Suite 200 Arlington Heights, IL 60004, USA

©2018 All Rights Reserved

### **Legal Disclaimer**

The information provided in this document shall in no event be regarded as a guarantee of conditions or characteristics. Tagore Technology assumes no responsibility for the consequences of the use of this information, nor for any infringement of patents or of other rights of third parties which may result from the use of this information. No license is granted by implication or otherwise under any patent or patent rights of Tagore Technology. The specifications mentioned in this document are subject to change without notice.

#### Information

For further information on technology, delivery terms and conditions and prices, please contact Tagore Technology: support@tagoretech.com.