Technical Data Sheet



SP5T Ramses SMA 18GHz Latching Self-cut-off Auto-reset 28Vdc

Diodes Pins Terminals

PAGE 1/2 ISSUE 22-03-22 SERIE : SPnT PART NUMBER : R573483500

RF CHARACTERISTICS

Number of ways : 5

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18
VSWR max	1.20	1.30	1.40	1.50
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB
Isolation min	80 dB	70 dB	60 dB	60 dB
Average power (*)	240 W	150 W	120 W	100 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING
Nominal current ** : 375 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / NEGATIVE COMMON
Terminals : solder pins (250°C max. / 30 sec.)

Self cut-off time : 40 ms < CT < 120 ms

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012 Life : 5 million cycles per position

Switching Time*** : < 40 ms Construction : Splashproof Weight : < 220 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

** At 25° C ±10%)

(*** Nominal voltage; 25° C)








SP5T Ramses SMA 18GHz Latching Self-cut-off Auto-reset 28Vdc Diodes Pins Terminals


ISSUE **22-03-22** SERIE : **SPnT** PART NUMBER : **R573483500**


DRAWING

PAGE **2/2**




Voltage	RF Continuity	
-C +1	$IN \leftrightarrow 1$	
-C +2	$IN \leftrightarrow 2$	
-C +3	$IN \leftrightarrow 3$	
-C +4	$IN \leftrightarrow 4$	
-C +5	IN ↔ 5	







SCHEMATIC DIAGRAM



General tolerances: ±0,5 mm [0,02 in]

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.