



SP6T Ramses SMA 18GHz Latching Self-cut-off Auto-reset Indicators 28Vdc BCD TTL Diodes Pins Terminals

PAGE 1/2 ISSUE 22-03-22 SERIE : SPnT PART NUMBER : R573493680

RF CHARACTERISTICS

Number of ways : 6

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18
VSWR max	1.20	1.30	1.40	1.50
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB
Isolation min	80 dB	70 dB	60 dB	60 dB
Average power (*)	240 W	150 W	120 W	100 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING
Nominal current ** : 375 mA

Actuator voltage (Vcc) : 28V (24 to 30V)

Terminals : solder pins (250°C max. / 30 sec.)

BCD inputs (E) - High level : 3.5 to 5.5 V / 800μA at 5.5 V - Low level : 0 to 1.5 V / 20μA at 0.8 V

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012 Life : 5 million cycles per position

Switching Time*** : < 40 ms Construction : Splashproof Weight : < 220 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)







SP6T Ramses SMA 18GHz Latching Self-cut-off Auto-reset Indicators 28Vdc BCD TTL Diodes Pins Terminals

PAGE **2/2** ISSUE **22-03-22** SERIE: SPnT PART NUMBER: **R573493680 DRAWING** 6 x M3 depth 4 ŝ 1.063 $\emptyset 27^{-}$ **BCD TRUTH TABLE** 0 0 E1 E3 E2 RF continuity Ind. All ports open 0 0 0 (Forced Reset) 0 $IN \leftrightarrow 1$ D.E 0 [1.508] 1 0 $IN \leftrightarrow 2$ D.F 0 0.8860 1 1 $IN \leftrightarrow 3$ D.G [0.256 min.] 6.50 min. 1 0 0 $\text{IN} \leftrightarrow 4$ D.H 1 0 1 D.I $IN \leftrightarrow 5$ Pin terminals $IN \leftrightarrow 6$ D.J 0 **LABEL RADIALL®** R573493680 [2.185 max.] 55.50 max. 0 - 18 GHz [0.303 max.] 7.70 max. Un: 28V GND BOTTOM VIEW Lot : _ _ _ _ 6 3 2 1 2.244 \emptyset 57 General tolerances: ±0,5 mm [0,02 in] **SCHEMATIC DIAGRAM** Power input RTN E2 E3 E1 Vcc terminals CUT-OFF / FORCED OR AUTOMATIC RESET BCD-TTL DRIVE D∳ Εφ Indicator terminals Actuators RF inputs n

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.