Data sheet

3SU1802-0AB00-2AB1



Enclosure for command devices, 22 mm, round, Enclosure material plastic, enclosure top part gray, 2 control points plastic, B=Pushbutton green, label: I, 1 NO, screw terminal, A=Pushbutton red, label: O, 1 NC, screw terminal, floor mounting, 1xM20 each on top and bottom, Labels enclosed

product brand name	SIRIUS ACT
product designation	Enclosures
product type designation	3SU1
equipment of commanding and signaling device	A = Pushbutton / B = Pushbutton
manufacturer's article number	
 of supplied contact module 	A1 = 3SU1400-2AA10-1CA0 / B2 = 3SU1400-2AA10-1BA0
 of supplied contact module at the command point A 	3SU1400-2AA10-1CA0
 of supplied contact module at the command point B 	3SU1400-2AA10-1BA0
 of the supplied holder 	A = 3SU1500-0AA10-0AA0, B = 3SU1500-0AA10-0AA0
 of the supplied holder at the command point A 	3SU1500-0AA10-0AA0
 of the supplied holder at the command point B 	3SU1500-0AA10-0AA0
 of the supplied actuator 	A = 3SU1000-0AB20-0AA0 / B = 3SU1000-0AB40-0AA0
 of the supplied actuator at the command point A 	3SU1000-0AB20-0AA0
 of the supplied actuator at the command point B 	3SU1000-0AB40-0AA0
 of supplied empty enclosure 	3SU1802-0AA00-0AB1
 of supplied accessory 	A = 3SU1900-0AF16-0QA0, B = 3SU1900-0AF16-0QB0
 of the supplied accessories at the command point A 	3SU1900-0AF16-0QA0
 of the supplied accessories at the command point B 	3SU1900-0AF16-0QB0
Enclosure	
design of the housing	with recess for label
shape of the enclosure front	rectangular
material of the enclosure	plastic
number of command points	2
product component	
 EMERGENCY STOP device 	No
protective collar	No
color of the enclosure top part	grey
delivery state	
• as a kit	No
pre-wired on strip terminal	No
fastening method of the enclosure	Vertical
Actuator	
design of the actuating element	Pushbutton / pushbutton
suitability for use EMERGENCY OFF switch	No
product feature lockout	No
product extension optional light source	No
color of the actuating element	A = red / B = green
material of the actuating element	plastic

shape of the actuating element	round
number of contact modules	2
type of unlocking device	A = none / B = none
Front ring	
product component front ring	Yes
design of the front ring	Standard
material of the front ring	plastic
color of the front ring	black
Holder	
material of the holder	Plastic
Display	
number of LED modules	0
General technical data	
product function	
 positive opening 	Yes
 EMERGENCY OFF function 	No
EMERGENCY STOP function	No
protection class IP	IP66, IP67, IP69(IP69K)
degree of protection NEMA rating	1, 2, 3, 3R, 4, 4X, 12K, 13
shock resistance	
 according to IEC 60068-2-27 	sinusoidal half-wave 15g / 11 ms
 for railway applications according to EN 61373 	Category 1, Class B
vibration resistance	
according to IEC 60068-2-6	10 500 Hz: 5g
 for railway applications according to EN 61373 	Category 1, Class B
reference code according to IEC 81346-2	S
continuous current of the C characteristic MCB	10 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A
continuous current of the DIAZED fuse link gG	10 A
Substance Prohibitance (Date)	10/01/2014
operating voltage	
• at AC	
— at 50 Hz rated value	5 500 V
— at 60 Hz rated value	5 500 V
at DC rated value	5 500 V
Communication/ Protocol	
design of the interface for communication	without
Auxiliary circuit	
design of the contact of auxiliary contacts	Silver alloy
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	1
Connections/ Terminals	
type of electrical connection of modules and accessories	Screw-type terminal
type of electrical connection on enclosure	Cable routing above and below, both 1 x M20
tightening torque of the screws in the bracket	1 1.2 N·m
tightening torque of fixing screws in the enclosure cover	1.5 1.7 N·m
tightening torque with screw-type terminals	0.8 0.9 N·m
Ambient conditions	
ambient temperature	
 during operation 	-25 +70 °C
during storage	-40 +80 °C
environmental category during operation according to IEC 60721	3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 95%, no condensation in operation permitted for all devices behind front panel)
Installation/ mounting/ dimensions	
fastening method of modules and accessories	Floor mounting
height	114 mm
width	85 mm
depth	75 mm

shape of the installation opening	round
Accessories	
number of labels	2
marking of the name plate for command devices	A = O / B = I
color of the label	A = black / B = black
number of inscription plates	0
Cortificatos/approvals	

Certificates/ approvals

General Product Approval



Confirmation









Declaration of Conformity

Test Certificates

Marine / Shipping



Type Test Certificates/Test Report

Special Test Certificate





Marine / Shipping

other







Environmental Confirmations

Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1802-0AB00-2AB1

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1802-0AB00-2AB1

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SU1802-0AB00-2AB1

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1802-0AB00-2AB1&lang=en

last modified:

1/26/2022

