SIEMENS

Data sheet

3SU1501-1AG00-1BA0



holder, 3-way, plastic, 1 NO, LED module, amber, 6-24 V AC/DC, screw terminal

product brand name	SIRIUS ACT
product designation	Holders
product type designation	3SU1
manufacturer's article number	
 of supplied contact module 	3SU1400-1AA10-1BA0
 of supplied contact module at position 1 	3SU1400-1AA10-1BA0
 of supplied LED module 	3SU1401-1BG00-1AA0
 of the supplied holder 	3SU1500-0AA10-0AA0
Actuator	
design of the actuating element	3-way with module
number of contact modules	1
Holder	
material of the holder	Plastic
Display	
number of LED modules	1
General technical data	
product function positive opening	No
product component	
• diode	Yes
 lamp transformer 	No
• light source	Yes
series resistor	No
insulation voltage rated value	320 V
degree of pollution	3
surge voltage resistance rated value	4 kV
protection class IP of the terminal	IP20
shock resistance	
• acc. to IEC 60068-2-27	Sinusoidal half-wave 50g / 11 ms
 for railway applications acc. to DIN EN 61373 	Category 1, Class B
vibration resistance	
• acc. to IEC 60068-2-6	10 500 Hz: 5g
for railway applications acc. to DIN EN 61373	Category 1, Class B
operating frequency maximum	3 600 1/h
mechanical service life (switching cycles) typical	10
thermal current	10 A
reference code acc. to IEC 81346-2	U
continuous current of the C characteristic MCB	10 A; for a short-circuit current smaller than 400 A

continuous current of the quick DIAZED fuse link	10 A
continuous current of the DIAZED fuse link gG	10 A
operating voltage at AC— at 50 Hz rated value	6 24 V
	6 24 V
— at 60 Hz rated value	6 24 V
operating voltage at DC rated value Power Electronics	0 24 V
	One male paration not 400 million (47 \ / 5 mA \ and male paration not 40
contact reliability	One maloperation per 100 million (17 V, 5 mA), one maloperation per 10 million (5 V, 1 mA)
Control circuit/ Control	
inrush current of LED module maximum	2 A
Auxiliary circuit	
design of the contact of auxiliary contacts	Silver alloy
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	1
operational current at AC-15 at 230 V rated value	6 A
Connections/ Terminals	
type of electrical connection	
 of modules and accessories 	Screw-type terminal
type of connectable conductor cross-sections	
 solid with core end processing 	2x (0.5 0.75 mm²)
 solid without core end processing 	2x (1.0 1.5 mm²)
 finely stranded with core end processing 	2x (0.5 1.5 mm²)
 finely stranded without core end processing 	2x (1,0 1,5 mm²)
at AWG cables	2x (18 14)
tightening torque of the screws in the bracket	1 1.2 N·m
• tightening torque with screw-type terminals	0.8 0.9 N·m
Lamp	
type of light source	LED
color of the light source	amber
light intensity	450 1 120 mcd
Ambient conditions	
ambient temperature during operation	-25 +70 °C
ambient temperature during storage	-40 +80 °C
environmental category during operation acc. to IEC 60721	3M6, 3S2, 3B2, 3K6 (with relative air humidity of 10 95 %, no condensation in operation permitted)
Installation/ mounting/ dimensions	
fastening method	front panel mounting
of modules and accessories	Front plate mounting
height	40 mm
width	30 mm
shape of the installation opening	round
installation width	30 mm
installation depth	49.8 mm
Certificates/ approvals	
General Product Approval	Declaration of Conformity
Ochoral Floudot Approval	Decidation of Comornity











Miscellaneous

Test Certificates other

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1501-1AG00-1BA0


Cax online generator


http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1501-1AG00-1BA0


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


https://support.industry.siemens.com/cs/ww/en/ps/3SU1501-1AG00-1BA0

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1501-1AG00-1BA0&lang=en









last modified: 8/29/2020 🖸