


| DRAWN | 7/20/2017 | CJ | CHECKED | P.D. | Dynamic Speaker | Dynamic Speaker | CJ | P/27/2017 | P/27/2017 | C.E. | P/27/2017 | C.E. | P/27/2017 | P/2

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com

## Top View

## Side View

## **Bottom View**



	3.0 +0.3 Working Position  0.7 -  1	Max. Vibration	0.5mm  Date Code Marking "17 G" 17=2017, G=Jul.	-XXX
--	-------------------------------------	----------------	---	------

3   -	- 10	_	
<b>T</b>	<u> </u>		
<u>+</u>			Î
,	1		-6.5
	. <u> </u>		,
	1		

	Items	Specifications	Conditions	<del></del>				
	Sound Pressure Level	92	dB (@ 10cm), Avg.			'		
	Resonant Frequency	550	Hz		REVISION HISTORY			
	Frequency Range	550 ~ 10,000	Hz	REV	DESCRIPTION	DATE	APPROVED	
	Nominal Power	0.75	W		Released from Engineering	9/27/2017	C.E.	
,	Max. Power	1	W	1	Updated SPL	7/13/2018	C.E.	
A	Impedance	8	Ω	NOTES				
	Cone Material	Mylar			All dimensions are in mm unless otherwise noted			
	Mount Type	Flush Mount		2) All tolerances are ± 0.2 mm unless otherwise noted				
	Storage Temperature	-20 ~ +55	°C	3) All parts meet RoHS				
	Operating Temperature	-20 ~ +55	°C		4) Subject to change or redrawn without notice			
	Weight	1.5	g					