

SP DYNAMIC SPEAKER UNIT

Acoustic Product Specification

Product Number: SP-1704



Release | Revision: A/2016

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1

Speaker Electroacoustic Characteristics

General Specifications

Page 2

Reliability Tests

Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

Page 4

Frequency Response Curve

Page 5

Dimensions

Page 6

Packing

Dynamic Speaker Electroacoustic Characteristics

Sound Pressure Level

 $89\pm3dB$ SPL @0.8, 1.0, 1.2, 1.5, 1.8 and 2.0KHz in average (0dB SPL=20 μ Pa) Measuring Condition:0.1W (Sine wave) 10cm measured with baffler shown in Fig.1

Frequency Response Curve

As shown in Figure 2

Response Frequency

850±20%Hz @ 1V. (without baffler)

Input Power (Nominal and Maximum)

Rated Noise Power: 0.8W

Short Term Max Power: 1.0W must be normal at a white noise (1W, F0 ~ 20KHz) for one minute

Operation Test

Must be free audible noise (buzzes and rattles)

300 ~ 5KHz frequency range, input level up to 2.53Vrms

Distortion

Less than 10% @1KHz, 0.1M, 0.5W frequency range, input level up to 2.0Vrms

General Specifications

Operating Temperature Range

-20°C~+60°C

Standard Test Conditions

Temperature 17°C~25°C

Relative Humidity 45%~80%(RH)

AC Impedance

 $8\pm15\%\Omega$ (@ 1.5KHz 1V) without baffler

Dimension

Ø17.0x4.0mm WIRE 38mm (UL1571 / AWG32#)

IP Level

IP50



SP DYNAMIC SPEAKER UNIT

Acoustic Product Specification

Product Number: SP-1704



Release | Revision: A/2016

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1

Speaker Electroacoustic Characteristics

General Specifications

Page 2

Reliability Tests

Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

Page 4

Frequency Response Curve

Page 5

Dimensions

Page 6

Packing

Reliability Tests

The sound pressure as specified will neither deviate more than ±3dB from the initial value, nor have any significant damage after any of following testing.

High Temperature Test

High Temperature +60±2°C

Duration 96 hours

Low Temperature Test

Low Temperature -20±2°C

Duration 96 hours

Heat Shock Test

High Temperature +60±2°C

Low Temperature -20±2°C

Changeover Time < 30 seconds

Duration 1 hour

Cycle 100

Humidity Test

Temperature +40±2°C

Relative Humidity 90%~95%

Duration 96 hours

Temperature Cycle Test

Temperature -20°C +60°C

Duration 45 minutes 45 minutes

Temperature gradient 1~3°C/min

Cycle 25

Drop Test

Mounted with dummy set mass $100\,\mathrm{g}$

Height 1.5 m

Cycle 6 (1 each plain) onto the concrete board

Load Test

Speaker mode: White noise (EIA filter) for 96 hours @ 0.8W input power.



SP DYNAMIC SPEAKER UNIT

Acoustic Product Specification

Product Number: SP-1704



Release | Revision: A/2016

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1

Speaker Electroacoustic Characteristics

General Specifications

Page 2

Reliability Tests

Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

Page 4

Frequency Response Curve

Page 5

Dimensions

Page 6

Packing

Measuring Method (Speaker Mode)

Standard Test Condition

Temperature 15 ~ 35°C

Relative humidity 45% ~ 85%

Atmospheric pressure 860mbar to 1060mbar

Standard Test Fixture

Input Power 0.1W (0.89V)


Zero Level -dB

Mode TSR

Potentiometer Range 50dB

Sweep Time 0.5sec

Standard Test Condition of Speaker (Fig, 1)





SP DYNAMIC SPEAKER UNIT

Acoustic Product Specification

Product Number: SP-1704



Release | Revision: A/2016

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1

Speaker Electroacoustic Characteristics

General Specifications

Page 2

Reliability Tests

Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of

Page 4

Frequency Response Curve


Page 5

Dimensions

Page 6

Packing

Frequency Response Curve (Fig. 2)





SP DYNAMIC SPEAKER UNIT

Acoustic Product Specification

Product Number: SP-1704



Release | Revision: A/2016

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1

Speaker Electroacoustic Characteristics

General Specifications

Page 2

Reliability Tests

Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

Page 4

Frequency Response Curve


Page 5


Dimensions

Page 6

Packing

Dimensions





No.	Part Name	Material	Quantity
1	UL1571 AWG32#	Wire Red/Black	2
2	PCB	Epoxy glass fiber	1
3	Frame	PBT	1
4	Magnet	Nd Fe B-N40	1
5	Plate	SPCC	1
6	Voice Coil	Copper	1
7	Membrane	PEN	1
8	Сар	SUS 304	1
9	Gasket	Polyester fiber	1
10	Damping net	Non-woven fabrics	1



SP DYNAMIC SPEAKER UNIT

Acoustic Product Specification

Product Number: SP-1704



Release | Revision: A/2016

CONTENTS

This document contains the technical specifications for the dynamic speaker unit.

Page 1

Speaker Electroacoustic Characteristics

General Specifications

Page 2

Reliability Tests

Page 3

Measuring Method (Speaker Mode)

Standard Test Condition of Speakers

Page 4

Frequency Response Curve

Page 5

Dimensions

Page 6

Packing

Packing

100PCS×10=1000PCS

